

Garant

**Clamping toolholder SVLCR 107,5°, for indexable inserts VC., right-hand,
Shank size / insert size: 8/07mm**



Order data

Order number	261306 8/07
GTIN	4045197948311
Item class	21T

Technical description

Overall length L	60 mm
Head length L ₁	15 mm
Shank size	8 mm
suitable indexable insert	VC.. 0702..
Insert size	7 mm
Pack of insert screws	269028 27
ISO code toolholder	SVLCR/L 0808D07
Functional width L ₄	10 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6