

Garant

**Clamping toolholder SVLCR 107,5°, for indexable inserts VC., right-hand,
Shank size / insert size: 12/07mm**


Order data

Order number	261306 12/07
GTIN	4045197948335
Item class	21T

Technical description

Functional width L ₄	16 mm
Pack of insert screws	269028 27
Shank size	12 mm
ISO code toolholder	SVLCR/L 1212F07
Overall length L	80 mm
Head length L ₁	18 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6