

**Garant****Tape measure mm/inch, Length: 5m**

## Order data

Order number	461910 5
GTIN	4045197949301
Item class	41H

## Description

### Version:

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

**Innovative dampers** of special rubber absorb the reaction energy and protect the wrist.

**Aluminium profile inserted** on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm/inch graduations

Reversible reading: mm / inch

Standard: EG II

Tape width: 16 mm

Body length: 70 mm

Body width: 30 mm

Body height: 69 mm

## Technical description

Tape width	16 mm
Body length	70 mm
Band length	5 m
Body width	30 mm
Body height	69 mm
Standard	EG II
Calibration	G1
Reversible reading	mm / inch
Type of product	Measuring tape

## Services

Calibration Tape measure maximum length 5 m	026240 5
---	----------