

Garant**Horizontal toggle clamp, variable, Type: 50****Order data**

Order number	376400 50
GTIN	4045197953315
Item class	31M

Description**Version:**

With horizontal base. Completely black nickel-plated, with solid rivets. Ergonomic 2-component handle. Captive contact screw. Complete with black nickel-plated contact screw.

Advantage:

Stepless adjustment function for variations in workpiece heights. Consistently high clamping forces.

Clamping force: 3000 N

automatic height adjustment S: 35 mm

maximum clamping height: 40 mm

Contact screw: M8×50 mm

Technical description

maximum clamping height	40 mm
Clamping force	3000 N
Contact screw	M8×50 mm
automatic height adjustment S	35 mm
Type of product	Horizontal toggle clamp

