



VDI multiple toolholder, overhead, Shank \varnothing d1: 30mm



Order data

Order number	319190 30
GTIN	4045197955074
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Standard:

DIN ISO 10889 / DIN 69880 / VDI 4325, Blatt 2.

Technical description

Shank width b_3	17 mm
Colour code for VDI shanks	VDI 30
Shank \varnothing D_1	30 mm
h_6	38 mm
b_1	76 mm
h_2	29 mm
h_5	28 mm

h_1	20 mm
b_2	35 mm
l_1	60 mm
Type of product	VDI multiple toolholder