

**VDI multiple toolholder, overhead, Shank \varnothing d1: 40mm****Order data**

Order number	319190 40
GTIN	4045197955081
Item class	32V

Description**Version:**

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Standard:

DIN ISO 10889 / DIN 69880 / VDI 4325, Blatt 2.

Technical description

h_1	25 mm
h_6	48 mm
h_2	34 mm
Colour code for VDI shanks	VDI 40
Shank width b_3	20.5 mm
h_5	32.5 mm
Shank \varnothing D ₁	40 mm

b_1	90 mm
l_1	72 mm
b_2	42.5 mm
Type of product	VDI multiple toolholder