


**Burr Z3 - medium, with chip breaker, HSS, Type: E1220****Order data**

Order number	540800 E1220
GTIN	4045197966872
Item class	52D

Description**Version:**

Shank Ø 6 mm.

HSS burrs for difficult vibration applications.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shank Ø	6 mm
Shape description	teardrop
Shape	E1220
Head Ø	12 mm
Overall length	60 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	20 mm
Series	#Tooth configuration Z3

Tool material	HSS
Type of product	Burr