

HOLEX**Universal clamp (clamping hand), Type: 150****Order data**

Order number	861900 150
GTIN	4045197167552
Item class	82C

Description**Version:**

With trapezoidal thread spindle and 2 swing clamping jaws. Each clamping jaw has 3 smooth faces and a cross-Vee face; can be used for **clamping the most diverse components**.

Application:

For **internal** and **external clamping** of the most diverse workpiece shapes.

Material:

Spindle and clamping block of burnished steel.

Technical description

Capacity in tension b	50 - 200 mm
maximum clamping force	3500 N
Clamping depth c	100 mm
Capacity in compression a	0 - 150 mm
Type of product	Clamp

