

**Burr Tooth profile INOX – coarse, Carbide, Type: A0820****Order data**

Order number	547250 A0820
GTIN	4045197973887
Item class	52D

Description**Version:**

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank Ø 6mm.

Application:

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

Technical description

Head Ø	8 mm
Shank Ø	6 mm
Tooth type abbreviation	INOX
Overall length	64 mm
Shape description	cylindrical
Toothing grit designation	coarse
Head length	19 mm
Series	STAINLESS STEEL tooth profile
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		