

**Burr Tooth profile INOX – coarse, Carbide, Type: C1225****Order data**

Order number	547250 C1225
GTIN	4045197973948
Item class	52D

Description**Version:**

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank \varnothing 6mm.

Application:

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

Technical description

Shape description	ball nose
Overall length	70 mm
Toothing grit designation	coarse
Head \varnothing	12.7 mm
Shank \varnothing	6 mm
Tooth type abbreviation	INOX
Head length	25 mm
Series	STAINLESS STEEL tooth profile
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		