


**Garant**

**Steel boring bar A.. SCLCL 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 0810/06mm**



## Order data

Order number	260032 0810/06
GTIN	4045197979001
Item class	21T

## Technical description

Insert size	6 mm
Overall length L	110 mm
ISO code toolholder	A0810J SCLCR/L06
Pack of insert screws	269028 7
Setting angle $\kappa$	95 degrees
Head length $L_1$	27 mm
Minimum pre-drill $\varnothing D_{\min}$	11 mm
suitable indexable insert	CC.. 0602..
Clamping height $L_2$	9 mm
Neck width $L_4$	8 mm
Centre offset $L_3$	6 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8