

Garant

Steel boring bar A.. SCLCL 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 1216/06mm



Order data

Order number	260032 1216/06
GTIN	4045197979025
Item class	21T

Technical description

Pack of insert screws	269028 7
Minimum pre-drill Ø D_{min}	16 mm
suitable indexable insert	CC.. 0602..
Setting angle κ	95 degrees
Insert size	6 mm
ISO code toolholder	A1216M SCLCR/L06
Clamping height L_2	15 mm
Overall length L	150 mm
Neck width L_4	12 mm
Centre offset L_3	8.9 mm
Head length L_1	42 mm
Shank Ø D_s	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8