

Garant

Steel boring bar A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 0810/07mm


Order data

Order number	260343 0810/07
GTIN	4045197979100
Item class	21T

Technical description

Head length L_1	22.5 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Pack of insert screws	269028 7
Insert size	7 mm
ISO code toolholder	A0810H SDUCR/L07
Neck width L_4	7 mm
Clamping height L_2	9 mm
Centre offset L_3	6.5 mm
Overall length L	100 mm
suitable indexable insert	DC.. 0702..
Setting angle κ	93 degrees
Usable depth T	4.4 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8