

Garant

Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 1216/07mm


Order data

Order number	260342 1216/07
GTIN	4045197979094
Item class	21T

Technical description

Neck width L_4	12 mm
ISO code toolholder	A1216M SDUCR/L07
Insert size	7 mm
Minimum pre-drill $\varnothing D_{min}$	18 mm
Setting angle κ	93 degrees
Clamping height L_2	15 mm
Pack of insert screws	269028 7
Centre offset L_3	11 mm
Overall length L	150 mm
suitable indexable insert	DC.. 0702..
Head length L_1	40.5 mm
Usable depth T	4.9 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8