

Garant

Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 0810/07mm


Order data

Order number	260342 0810/07
GTIN	4045197979070
Item class	21T

Technical description

Overall length L	100 mm
Clamping height L ₂	9 mm
Head length L ₁	22.5 mm
Insert size	7 mm
Minimum pre-drill Ø D _{min}	12.5 mm
Pack of insert screws	269028 7
Neck width L ₄	7 mm
Setting angle κ	93 degrees
suitable indexable insert	DC.. 0702..
ISO code toolholder	A0810H SDUCR/L07
Centre offset L ₃	6.5 mm
Usable depth T	4.4 mm
Shank Ø D _s	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8