

**Garant**

**Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 1012/07mm**


**Order data**

Order number	260342 1012/07
GTIN	4045197979087
Item class	21T

**Technical description**

ISO code toolholder	A1012K SDUCR/L07
Neck width L <sub>4</sub>	9 mm
suitable indexable insert	DC.. 0702..
Head length L <sub>1</sub>	27.5 mm
Overall length L	125 mm
Minimum pre-drill Ø D <sub>min</sub>	15.5 mm
Setting angle κ	93 degrees
Pack of insert screws	269028 7
Clamping height L <sub>2</sub>	11 mm
Centre offset L <sub>3</sub>	9 mm
Insert size	7 mm
Usable depth T	5.9 mm
Shank Ø D <sub>s</sub>	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8