

Garant

Steel boring bar A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 1012/07mm


Order data

Order number	260343 1012/07
GTIN	4045197979117
Item class	21T

Technical description

Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Neck width L_4	9 mm
ISO code toolholder	A1012K SDUCR/L07
Minimum pre-drill $\varnothing D_{min}$	15.5 mm
Setting angle κ	93 degrees
Head length L_1	27.5 mm
Insert size	7 mm
Overall length L	125 mm
Clamping height L_2	11 mm
Centre offset L_3	9 mm
Usable depth T	5.9 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8