

**Garant**

**Steel boring bar A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 1216/07mm**


**Order data**

Order number	260343 1216/07
GTIN	4045197979124
Item class	21T

**Technical description**

Clamping height $L_2$	15 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	18 mm
Setting angle $\kappa$	93 degrees
Neck width $L_4$	12 mm
ISO code toolholder	A1216M SDUCR/L07
Head length $L_1$	40.5 mm
Overall length $L$	150 mm
Insert size	7 mm
Centre offset $L_3$	11 mm
Pack of insert screws	269028 7
Usable depth $T$	4.9 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8