

Garant**Top jaw Gripp, single piece, for type: 125GS****Order data**

Order number	361123 125GS
GTIN	4045197985941
Item class	310

Description**Version:**

Clamping step with a height of 5 mm and 3 mm contact area.

Application:

Ideal for rough machining.

Suitable for:

5-axis vice set No. 361100 and clamping module No. 361105 – 361110.

Supplied with:

Fastening screws.

Note:

Type GS with gripp step and smooth clamping step

Technical description

suitable for colour code	Xpent1-2
Length l_1	3 mm
Jaw length l	68.5 mm
Length l_2	3 mm
Jaw width b	125 mm
Height h_1	5 mm

Jaw height h	45 mm
Height h ₂	5 mm
Type of product	Vice jaws