

**ER mini collet holder cylindrical, for ER collet size: 8****Order data**

Order number	300684 8
GTIN	4045197700810
Item class	32A

Description**Version:**

Cylindrical holder with ER nut.

Through hole for internal cooling provided.

Application:

For extending the reach of side lock arbors or collet chucks.

Optional extras:

Clamping wrenches No. 309740 and No. 309745.

ER collets No. 308878 – 309434, Spare ER nuts No. 309580; 309650.

Note:

Not suitable for shrink processes. No length adjustment available.

Technical description

Shank Ø d	12 mm
for ER collets	8 mm
Shank length L ₁	70 mm
Clamping range	1 - 5 mm
L ₂	15.6 mm
External Ø D	12 mm
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm

Machining strategy	HSC
Type of product	Collet chuck

Accessories

ER collet Nominal clamping Ø d 20 mm	309000 20
ER collet Nominal clamping Ø d 11 mm	308930 11
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309430 9
ER colletwith seal Nominal clamping Ø d 7 mm	308986 7
ER colletwith seal Nominal clamping Ø d 6 mm	308986 6
ER colletwith seal Nominal clamping Ø d 10 mm	308921 10
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 12 mm	309448 12
ER colletwith seal Nominal clamping Ø d 5 mm	308946 5
ER collet HPwith seal Nominal clamping Ø d 3 mm	309377 3
ER colletwith seal Nominal clamping Ø d 6 mm	308921 6
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309414 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 15 mm	309002 15
ER clamping nutfor sealing rings for ER 25	309615 25
ER collet for machine tapswith seal Nominal clamping Ø d 4,5 mm	309402 4,5
ER clamping nutHigh Speed for ER 40	309610 40
ER collet Nominal clamping Ø d 25 mm	309040 25
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309425 3,5
ER collet HP Nominal clamping Ø d 16 mm	309376 16
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309448 4,5

ER collet HPwith seal Nominal clamping Ø d 5 mm	309371 5
ER colletwith seal and spray nozzles Nominal clamping Ø d 19 mm	309002 19
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 4 mm	309372 4
ER collet for machine tapswith seal Nominal clamping Ø d 3,5 mm	309402 3,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309448 6
ER collet for machine tapswith seal Nominal clamping Ø d 4 mm	309406 4
ER collet HPwith seal Nominal clamping Ø d 4 mm	309369 4
ER collet HP Nominal clamping Ø d 3 mm	309368 3
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 8 mm	309404 8
ER collet Nominal clamping Ø d 5 mm	308911 5
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 18 mm	309378 18
ER collet Nominal clamping Ø d 16 mm	308990 16
ER colletwith seal Nominal clamping Ø d 7 mm	309001 7
ER collet HP Nominal clamping Ø d 7 mm	309373 7
ER collet Nominal clamping Ø d 18 mm	309000 18
ER collet Nominal clamping Ø d 7 mm	308990 7
ER colletwith seal Nominal clamping Ø d 9 mm	308946 9
ER colletwith seal and spray nozzles Nominal clamping Ø d 9 mm	308962 9
ER collet set 12 pieces 2–13 mm	309016
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309409 14
ER collet Nominal clamping Ø d 13 mm	308990 13
ER collet HP Nominal clamping Ø d 4 mm	309373 4
ER colletwith seal and spray nozzles Nominal clamping Ø d 5 mm	308962 5

ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309414 8
ER colletwith seal Nominal clamping Ø d 8 mm	308946 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 4 mm	308922 4
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309432 4,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309445 6
ER collet for machine tapswith seal Nominal clamping Ø d 4,5 mm	309414 4,5
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309416 11
ER collet Nominal clamping Ø d 8 mm	308911 8
ER collet for machine tapswith seal Nominal clamping Ø d 4,5 mm	309416 4,5
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 7 mm	309413 7
ER collet set 7 pieces 1–7 mm	309155
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309411 6
ER collet HP Nominal clamping Ø d 15 mm	309373 15
ER collet Nominal clamping Ø d 1,5 mm	308881 1,5
ER collet HP Nominal clamping Ø d 3 mm	309379 3
ER collet Nominal clamping Ø d 26 mm	308990 26
ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309402 9
ER collet Nominal clamping Ø d 7 mm	308960 7
ER collet Nominal clamping Ø d 12 mm	309000 12
ER colletwith seal Nominal clamping Ø d 6 mm	309001 6
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309411 11
	309448 9

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 9 mm

ER colletwith seal Nominal clamping Ø d 13 mm	308959 13
---	-----------

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309445 4
--	----------

ER colletwith seal and spray nozzles Nominal clamping Ø d 4 mm	309002 4
--	----------

ER collet HPwith seal Nominal clamping Ø d 9 mm	309371 9
---	----------

ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309414 18
--	-----------

ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 4,5 mm	309404 4,5
---	------------

ER collet Nominal clamping Ø d 16 mm	308941 16
--------------------------------------	-----------

ER collet Nominal clamping Ø d 10 mm	308920 10
--------------------------------------	-----------

ER collet Nominal clamping Ø d 1 mm	308918 1
-------------------------------------	----------

ER colletwith seal Nominal clamping Ø d 13 mm	308986 13
---	-----------

ER collet HP Nominal clamping Ø d 16 mm	309379 16
---	-----------

ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309430 6
---	----------

ER colletwith seal Nominal clamping Ø d 6 mm	308946 6
--	----------

ER collet HPwith seal Nominal clamping Ø d 6 mm	309369 6
---	----------

ER collet HP Nominal clamping Ø d 13 mm	309373 13
---	-----------

ER collet Nominal clamping Ø d 17 mm	308981 17
--------------------------------------	-----------

ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309403 9
---	----------

ER colletwith seal and spray nozzles Nominal clamping Ø d 12 mm	309002 12
---	-----------

ER collet Nominal clamping Ø d 15 mm	308981 15
--------------------------------------	-----------

ER collet Nominal clamping Ø d 4 mm	308960 4
-------------------------------------	----------

ER colletwith seal Nominal clamping Ø d 12 mm	308916 12
---	-----------

ER collet set 15 pieces 2–16 mm	309240
---------------------------------	--------

ER colletwith seal Nominal clamping Ø d 18 mm	309001 18
---	-----------

ER collet Nominal clamping Ø d 6 mm	308920 6
ER collet Nominal clamping Ø d 24 mm	308990 24
ER collet HP Nominal clamping Ø d 5 mm	309379 5
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309411 16
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309419 6
ER clamping nut for ER 25	309580 25
ER collet HP Nominal clamping Ø d 8 mm	309373 8
ER clamping nutHigh Speed for ER 25	309610 25
ER collet Nominal clamping Ø d 5 mm	308960 5
ER collet HP Nominal clamping Ø d 20 mm	309379 20
ER collet HP Nominal clamping Ø d 9 mm	309370 9
ER colletwith seal Nominal clamping Ø d 4 mm	308986 4
ER collet Nominal clamping Ø d 4 mm	308881 4
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309409 7
ER colletwith seal Nominal clamping Ø d 16 mm	308986 16
ER collet Nominal clamping Ø d 11 mm	309000 11
ER collet Nominal clamping Ø d 21 mm	309040 21
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309414 7
ER collet Nominal clamping Ø d 5 mm	309000 5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309447 3,5
ER collet Nominal clamping Ø d 1,5 mm	308878 1,5
ER collet Nominal clamping Ø d 2 mm	308901 2
ER colletwith seal Nominal clamping Ø d 19 mm	309001 19
ER collet Nominal clamping Ø d 8 mm	308930 8
ER collet Nominal clamping Ø d 8 mm	308990 8
ER colletwith seal Nominal clamping Ø d 11 mm	309001 11

ER collet Nominal clamping Ø d 18 mm	308981 18
ER collet HPwith seal Nominal clamping Ø d 3 mm	309374 3
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309416 12
ER colletwith seal Nominal clamping Ø d 3 mm	308921 3
ER collet Nominal clamping Ø d 11 mm	308960 11
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309416 16
ER collet HPwith seal Nominal clamping Ø d 3 mm	309369 3
ER collet Nominal clamping Ø d 4 mm	308930 4
ER collet set 18 pieces 3–20 mmwith seal and spray nozzles	309285
ER collet Nominal clamping Ø d 6 mm	308918 6
ER collet HP Nominal clamping Ø d 19 mm	309376 19
ER collet HPwith seal Nominal clamping Ø d 15 mm	309377 15
ER collet Nominal clamping Ø d 9 mm	308960 9
ER colletwith seal Nominal clamping Ø d 4 mm	308882 4
ER collet Nominal clamping Ø d 1 mm	308920 1
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309419 14
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 7 mm	309404 7
ER collet set 8 pieces 4–16, 20 mmwith seal	309026
ER collet Nominal clamping Ø d 9 mm	309040 9
ER colletwith seal Nominal clamping Ø d 11 mm	308916 11
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309414 14
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309411 7
ER colletwith seal and spray nozzles Nominal clamping Ø d 10 mm	308962 10
ER collet HP Nominal clamping Ø d 22 mm	309379 22
	309432 12

ET collet for thread tapping, with axial compensation
Nominal clamping Ø d 12 mm

ER colletwith seal Nominal clamping Ø d 14 mm	308946 14
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 3,5 mm	309404 3,5
ER collet Nominal clamping Ø d 10 mm	308911 10
ER colletwith seal Nominal clamping Ø d 16 mm	308959 16
ER collet set 23 pieces 4–26 mm	309028
ER collet set 18 pieces 3–20 mmwith seal	309284
ER collet HP Nominal clamping Ø d 11 mm	309379 11
ER collet Nominal clamping Ø d 25 mm	308990 25
ER colletwith seal Nominal clamping Ø d 12 mm	308946 12
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 14 mm	309375 14
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309432 9
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 12 mm	309418 12
ER colletwith seal Nominal clamping Ø d 13 mm	309001 13
ER collet Nominal clamping Ø d 5 mm	308981 5
ER collet HPwith seal Nominal clamping Ø d 14 mm	309377 14
ER collet Nominal clamping Ø d 2 mm	308960 2
ER collet for machine tapswith seal Nominal clamping Ø d 20 mm	309416 20
ER collet HP Nominal clamping Ø d 3 mm	309373 3
ER collet HPwith seal Nominal clamping Ø d 11 mm	309377 11
ER collet HPwith seal Nominal clamping Ø d 19 mm	309377 19
ER colletwith seal and spray nozzles Nominal clamping Ø d 9 mm	308922 9
ER collet set HPwith seal (3; 4; 5; 6; 8; 10mm), 425 E	309391
ER collet HP Nominal clamping Ø d 6 mm	309373 6
	309402 7

ER collet for machine taps with seal Nominal clamping Ø d 7 mm

ER collet Nominal clamping Ø d 11 mm

308990 11

ER collet for machine taps with seal Nominal clamping Ø d 7 mm

309406 7

ER collet with seal Nominal clamping Ø d 4 mm

308921 4

ER collet with seal and spray nozzles Nominal clamping Ø d 18 mm

309002 18

ER collet Nominal clamping Ø d 7 mm

308930 7

ER collet Nominal clamping Ø d 5 mm

308901 5

ER collet with seal Nominal clamping Ø d 14 mm

308959 14

ER collet Nominal clamping Ø d 4 mm

308878 4

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2,8 mm

309445 2,8

ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm

308922 5

ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 9 mm

309413 9

ER plain bearing clamping nut for ER 40

309612 40

ER collet with seal Nominal clamping Ø d 5 mm

308986 5

ER collet Nominal clamping Ø d 5,5 mm

308881 5,5

ER collet with seal and spray nozzles Nominal clamping Ø d 16 mm

309002 16

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm

309448 10

ER collet with seal Nominal clamping Ø d 8 mm

308916 8

ER collet Nominal clamping Ø d 24 mm

309040 24

ER collet with seal Nominal clamping Ø d 25 mm

308992 25

ER collet with seal Nominal clamping Ø d 7 mm

308946 7

ER collet HP with seal Nominal clamping Ø d 7 mm

309371 7

ER clamping nut for ER 32

309580 32

ER collet HP with seal Nominal clamping Ø d 16 mm

309374 16

ER colletwith seal and spray nozzles Nominal clamping Ø d 6 mm	308962 6
ER collet HPwith seal Nominal clamping Ø d 9 mm	309377 9
ER colletwith seal Nominal clamping Ø d 5 mm	308882 5
ER collet Nominal clamping Ø d 5 mm	308920 5
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309406 10
ER collet Nominal clamping Ø d 3 mm	308930 3
ER colletwith seal and spray nozzles Nominal clamping Ø d 6 mm	309002 6
ER collet Nominal clamping Ø d 6 mm	308960 6
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309416 6
ER collet Nominal clamping Ø d 11 mm	308941 11
ER collet Nominal clamping Ø d 9 mm	309000 9
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 20 mm	309418 20
ER collet for machine tapswith seal Nominal clamping Ø d 2,8 mm	309402 2,8
ER collet for machine tapswith seal Nominal clamping Ø d 22 mm	309419 22
ER collet Nominal clamping Ø d 2,5 mm	308901 2,5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309432 6
ER collet HPwith seal Nominal clamping Ø d 10 mm	309374 10
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309402 8
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309414 10
ER collet HPwith seal Nominal clamping Ø d 10 mm	309377 10
ER clamping nutfor sealing rings for ER 32	309615 32
ER collet HPwith seal Nominal clamping Ø d 13 mm	309377 13
	309445 2

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2 mm

ER collet for machine taps with seal Nominal clamping Ø d 8 mm

309409 8

ER collet Nominal clamping Ø d 4,5 mm

308881 4,5

ER clamping nut for ER 40

309580 40

ER clamping nut for HiRun ER collet chucks for ER 16

309617 16

ER collet HP with seal and spray nozzles Nominal clamping Ø d 10 mm

309378 10

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm

309448 4

ER collet with seal Nominal clamping Ø d 4 mm

309001 4

ER collet HP Nominal clamping Ø d 2 mm

309368 2

ER collet for machine taps with seal Nominal clamping Ø d 10 mm

309411 10

ER collet Nominal clamping Ø d 7 mm

308918 7

ER collet Nominal clamping Ø d 3,5 mm

308881 3,5

ER collet with seal Nominal clamping Ø d 7 mm

308959 7

ER collet Nominal clamping Ø d 21 mm

308990 21

ER collet HP Nominal clamping Ø d 15 mm

309376 15

ER collet Nominal clamping Ø d 5 mm

308881 5

ER collet for machine taps with seal Nominal clamping Ø d 20 mm

309419 20

ER collet HP Nominal clamping Ø d 9 mm

309376 9

ER collet HP with seal Nominal clamping Ø d 11 mm

309374 11

ER collet Nominal clamping Ø d 6 mm

308930 6

ER collet Nominal clamping Ø d 17 mm

309000 17

ER collet Nominal clamping Ø d 4 mm

308901 4

ER collet set 13 pieces 1–7 mm

309010

ER collet HP Nominal clamping Ø d 12 mm

309373 12

ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 10 mm

309418 10

ER collet HP Nominal clamping Ø d 12 mm	309379 12
ER collet Nominal clamping Ø d 10 mm	308960 10
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309419 16
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309445 3,5
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309416 14
ER collet set 10 pieces 1–10 mm	309160
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 4,5 mm	309418 4,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 7 mm	309447 7
ER colletwith seal and spray nozzles Nominal clamping Ø d 17 mm	309002 17
ER collet HPwith seal Nominal clamping Ø d 10 mm	309371 10
ER collet HP Nominal clamping Ø d 9 mm	309379 9
ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309416 18
ER colletwith seal and spray nozzles Nominal clamping Ø d 3 mm	308922 3
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 8 mm	309378 8
ER colletwith seal Nominal clamping Ø d 9 mm	308959 9
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 11 mm	309448 11
ER colletwith seal and spray nozzles Nominal clamping Ø d 3 mm	308962 3
ER collet Nominal clamping Ø d 4,5 mm	308878 4,5
ER collet HP Nominal clamping Ø d 8 mm	309376 8
ER collet HPwith seal Nominal clamping Ø d 16 mm	309377 16
ER collet Nominal clamping Ø d 15 mm	309040 15
ER collet Nominal clamping Ø d 6 mm	308881 6

ER collet Nominal clamping Ø d 10 mm	308901 10
ER collet HP Nominal clamping Ø d 10 mm	309376 10
ER colletwith seal Nominal clamping Ø d 17 mm	308986 17
ER colletwith seal Nominal clamping Ø d 15 mm	308986 15
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309403 8
ER colletwith seal Nominal clamping Ø d 16 mm	309001 16
ER colletwith seal Nominal clamping Ø d 5 mm	308921 5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309430 4,5
ER colletwith seal Nominal clamping Ø d 12 mm	308959 12
ER Mini clamping nut for ER 20	309650 20
ER colletwith seal Nominal clamping Ø d 6 mm	308916 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309447 4
ER colletwith seal and spray nozzles Nominal clamping Ø d 13 mm	308962 13
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 14 mm	309378 14
ER collet Nominal clamping Ø d 10 mm	308930 10
ER collet Nominal clamping Ø d 19 mm	308990 19
ER collet HP Nominal clamping Ø d 5 mm	309373 5
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 14 mm	309418 14
ER colletwith seal Nominal clamping Ø d 5 mm	308916 5
ER collet set 10 pieces 1–10 mmwith seal and spray nozzles	309165
ER collet Nominal clamping Ø d 3 mm	308911 3
ER colletwith seal and spray nozzles Nominal clamping Ø d 11 mm	308962 11
ER colletwith seal Nominal clamping Ø d 6 mm	308992 6
ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309406 9

ER collet set 18 pieces 3–20 mm	309280
ER collet set 7 pieces 4–16 mm with seal	309022
ER collet HP with seal Nominal clamping Ø d 7 mm	309374 7
ER collet with seal and spray nozzles Nominal clamping Ø d 14 mm	308962 14
ER collet Nominal clamping Ø d 8 mm	309000 8
ER collet with seal Nominal clamping Ø d 13 mm	308946 13
ER collet HP with seal Nominal clamping Ø d 4 mm	309371 4
ER clamping nut High Speed for ER 16	309610 16
ER collet with seal Nominal clamping Ø d 3 mm	309001 3
ER collet with seal Nominal clamping Ø d 18 mm	308992 18
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309416 8
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309419 11
ER collet for machine taps with seal Nominal clamping Ø d 3,5 mm	309406 3,5
ER plain bearing clamping nut for ER 32	309612 32
ER collet Nominal clamping Ø d 3 mm	309000 3
ER collet with seal Nominal clamping Ø d 3 mm	308916 3
ER collet with seal Nominal clamping Ø d 20 mm	308986 20
ER collet Nominal clamping Ø d 4 mm	308918 4
ER collet Nominal clamping Ø d 2,5 mm	308881 2,5
ER collet Nominal clamping Ø d 7 mm	308941 7
ER collet Nominal clamping Ø d 7 mm	308981 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 8 mm	309447 8
ER collet Nominal clamping Ø d 17 mm	308990 17
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309419 7
ER collet HP Nominal clamping Ø d 4 mm	309368 4

ER collet HP Nominal clamping Ø d 26 mm	309379 26
ER collet Nominal clamping Ø d 5 mm	309040 5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309430 3,5
ER collet HP Nominal clamping Ø d 14 mm	309376 14
ER colletwith seal Nominal clamping Ø d 10 mm	309001 10
ER collet HPwith seal Nominal clamping Ø d 6 mm	309374 6
ER colletwith seal Nominal clamping Ø d 20 mm	308992 20
ER colletwith seal Nominal clamping Ø d 11 mm	308959 11
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309445 4,5
ER collet Nominal clamping Ø d 22 mm	309040 22
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309430 8
ER collet set HPwith seal (4; 6; 8; 10; 12; 14; 16mm) 429 E	309394
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309447 4,5
ER colletwith seal Nominal clamping Ø d 20 mm	309001 20
ER colletwith seal Nominal clamping Ø d 19 mm	308986 19
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309416 10
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309409 16
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309419 10
ER colletwith seal Nominal clamping Ø d 3 mm	308906 3
ER collet Nominal clamping Ø d 13 mm	308941 13
ER collet Nominal clamping Ø d 6 mm	308990 6
ER collet Nominal clamping Ø d 7 mm	309040 7
ER collet Nominal clamping Ø d 7 mm	309000 7
ER collet Nominal clamping Ø d 3 mm	308918 3
	309411 4,5

ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm

ER collet HP with seal Nominal clamping Ø d 8 mm	309371 8
ER collet with seal Nominal clamping Ø d 12 mm	308986 12
ER collet with seal Nominal clamping Ø d 4 mm	308916 4
ER collet Nominal clamping Ø d 18 mm	309040 18
ER clamping nut High Speed for ER 32	309610 32
ER collet with seal Nominal clamping Ø d 9 mm	308916 9
ER collet HP Nominal clamping Ø d 5 mm	309365 5
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309416 9
ER collet Nominal clamping Ø d 2,5 mm	308911 2,5
ER collet Nominal clamping Ø d 6 mm	308911 6
ER collet set 9 pieces 1–5 mm	309008
ER collet HP Nominal clamping Ø d 7 mm	309368 7
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309425 2,8
ER collet Nominal clamping Ø d 15 mm	309000 15
ER collet Nominal clamping Ø d 12 mm	308990 12
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 6 mm	309418 6
ER collet HP Nominal clamping Ø d 4 mm	309376 4
ER collet HP with seal and spray nozzles Nominal clamping Ø d 12 mm	309381 12
ER collet HP with seal and spray nozzles Nominal clamping Ø d 4 mm	309378 4
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 9 mm	309447 9
ER clamping nut for HiRun ER collet chucks for ER 40	309617 40
ER plain bearing clamping nut for ER 25	309612 25
ER collet HP with seal and spray nozzles Nominal clamping Ø d 12 mm	309378 12

ER collet Nominal clamping Ø d 6,5 mm	308881 6,5
ER colletwith seal Nominal clamping Ø d 3 mm	308882 3
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 7 mm	309448 7
ER colletwith seal and spray nozzles Nominal clamping Ø d 7 mm	308922 7
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 9 mm	309418 9
ER collet Nominal clamping Ø d 11 mm	308911 11
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 20 mm	309378 20
ER collet Nominal clamping Ø d 18 mm	308990 18
ER collet Nominal clamping Ø d 7 mm	308881 7
ER collet HPwith seal Nominal clamping Ø d 8 mm	309377 8
ER colletwith seal Nominal clamping Ø d 5 mm	308906 5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309447 6
ER collet HP Nominal clamping Ø d 15 mm	309379 15
ER collet HP Nominal clamping Ø d 10 mm	309379 10
ER collet Nominal clamping Ø d 19 mm	308981 19
ER collet set 7 pieces 3, 4, 5, 6, 8, 10, 12 mmwith seal	309018
ER Mini clamping nut for ER 16	309650 16
ER collet Nominal clamping Ø d 6 mm	308901 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 10 mm	308922 10
ER colletwith seal and spray nozzles Nominal clamping Ø d 4 mm	308962 4
ER collet Nominal clamping Ø d 14 mm	309000 14
ER collet Nominal clamping Ø d 10 mm	308990 10
ER clamping nutfor sealing rings for ER 16	309615 16
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 8 mm	309413 8

ER collet Nominal clamping Ø d 5 mm	308918 5
ER collet HPwith seal Nominal clamping Ø d 20 mm	309377 20
ER collet HPwith seal Nominal clamping Ø d 5 mm	309369 5
ER collet HPwith seal Nominal clamping Ø d 12 mm	309374 12
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309403 6
ER collet Nominal clamping Ø d 6 mm	308981 6
ER collet Nominal clamping Ø d 10 mm	308981 10
ER colletwith seal Nominal clamping Ø d 4 mm	308946 4
ER collet HP Nominal clamping Ø d 3 mm	309365 3
ER collet Nominal clamping Ø d 14 mm	308941 14
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309419 12
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309409 10
ER collet Nominal clamping Ø d 7 mm	308920 7
ER colletwith seal Nominal clamping Ø d 12 mm	308992 12
ER colletwith seal Nominal clamping Ø d 10 mm	308986 10
ER collet Nominal clamping Ø d 1 mm	308901 1
ER colletwith seal Nominal clamping Ø d 10 mm	308959 10
ER collet HP Nominal clamping Ø d 8 mm	309370 8
ER collet Nominal clamping Ø d 3 mm	308941 3
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309447 3
ER collet HP Nominal clamping Ø d 13 mm	309376 13
ER colletwith seal Nominal clamping Ø d 8 mm	308986 8
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 14 mm	309448 14
ER collet Nominal clamping Ø d 23 mm	309040 23
ER collet Nominal clamping Ø d 6 mm	308941 6
ER collet Nominal clamping Ø d 20 mm	308981 20

ER collet Nominal clamping Ø d 4 mm	309040 4
ER collet Nominal clamping Ø d 4 mm	308981 4
ER collet HP Nominal clamping Ø d 5 mm	309376 5
ER collet Nominal clamping Ø d 11 mm	309040 11
ER collet Nominal clamping Ø d 2 mm	308881 2
ER collet HP Nominal clamping Ø d 23 mm	309379 23
ER collet Nominal clamping Ø d 4 mm	308920 4
ER collet HPwith seal Nominal clamping Ø d 5 mm	309374 5
ER collet Nominal clamping Ø d 12 mm	308911 12
ER collet Nominal clamping Ø d 9 mm	308941 9
ER collet HPwith seal Nominal clamping Ø d 18 mm	309377 18
ER collet HPwith seal Nominal clamping Ø d 5 mm	309377 5
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309409 11
ER collet HP Nominal clamping Ø d 1 mm	309365 1
ER collet HP Nominal clamping Ø d 2 mm	309370 2
ER colletwith seal Nominal clamping Ø d 11 mm	308986 11
ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309414 9
ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309411 9
ER collet HPwith seal Nominal clamping Ø d 9 mm	309374 9
ER collet Nominal clamping Ø d 8 mm	308941 8
ER collet HP Nominal clamping Ø d 3 mm	309376 3
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309403 7
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309414 16
ER colletwith seal and spray nozzles Nominal clamping Ø d 6 mm	308922 6
ER collet HP Nominal clamping Ø d 2 mm	309373 2

ER collet Nominal clamping Ø d 8 mm	308920 8
ER collet HP Nominal clamping Ø d 2 mm	309376 2
ER colletwith seal Nominal clamping Ø d 3 mm	308946 3
ER colletwith seal Nominal clamping Ø d 4 mm	308906 4
ER collet HP Nominal clamping Ø d 11 mm	309373 11
ER collet Nominal clamping Ø d 13 mm	309000 13
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 11 mm	309418 11
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309419 8
ER collet Nominal clamping Ø d 15 mm	308941 15
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 4,5 mm	309413 4,5
ER collet HP Nominal clamping Ø d 10 mm	309373 10
ER collet HP Nominal clamping Ø d 6 mm	309376 6
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 12 mm	309413 12
ER colletwith seal Nominal clamping Ø d 9 mm	308921 9
ER colletwith seal Nominal clamping Ø d 14 mm	308986 14
ER collet set 18 pieces 3–20 mm	309024
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309425 6
ER collet for machine tapswith seal Nominal clamping Ø d 2,8 mm	309403 2,8
ER Mini clamping nut for ER 8	309650 8
ER collet HPwith seal Nominal clamping Ø d 3 mm	309371 3
ER collet Nominal clamping Ø d 2 mm	308918 2
ER collet Nominal clamping Ø d 12 mm	309040 12
ER colletwith seal Nominal clamping Ø d 15 mm	308946 15
ER colletwith seal Nominal clamping Ø d 11 mm	308946 11
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309414 11

ER collet Nominal clamping Ø d 4 mm	309000 4
ER collet Nominal clamping Ø d 14 mm	308990 14
ER collet Nominal clamping Ø d 14 mm	309040 14
ER collet set 15 pieces 2–16 mm with seal	309244
ER collet with seal Nominal clamping Ø d 14 mm	309001 14
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309449 10
ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309414 12
ER collet HP Nominal clamping Ø d 18 mm	309379 18
ER collet with seal Nominal clamping Ø d 8 mm	308992 8
ER collet HP Nominal clamping Ø d 9 mm	309373 9
ER collet with seal Nominal clamping Ø d 8 mm	308921 8
ER collet set HP(3; 4; 5; 6; 8; 10mm), 426 E	309390
ER collet Nominal clamping Ø d 19 mm	309040 19
ER collet Nominal clamping Ø d 5 mm	308930 5
ER collet HP with seal and spray nozzles Nominal clamping Ø d 4 mm	309375 4
ER collet HP Nominal clamping Ø d 17 mm	309376 17
ER collet HP Nominal clamping Ø d 7 mm	309379 7
ER collet with seal Nominal clamping Ø d 9 mm	308986 9
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309445 3
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309445 5
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 18 mm	309418 18
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309403 4,5
ER collet HP with seal Nominal clamping Ø d 13 mm	309374 13
ER collet Nominal clamping Ø d 1,5 mm	308901 1,5
ER plain bearing clamping nut for ER 16	309612 16

ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309419 9
ER collet Nominal clamping Ø d 10 mm	308941 10
ER collet HP Nominal clamping Ø d 16 mm	309373 16
ER collet Nominal clamping Ø d 13 mm	309040 13
ER collet Nominal clamping Ø d 2,5 mm	308878 2,5
ER collet HP Nominal clamping Ø d 5 mm	309368 5
ER collet Nominal clamping Ø d 8 mm	308981 8
ER collet for machine tapswith seal Nominal clamping Ø d 25 mm	309419 25
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309416 7
ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309419 18
ER collet Nominal clamping Ø d 9 mm	308911 9
ER colletwith seal and spray nozzles Nominal clamping Ø d 8 mm	308922 8
ER colletwith seal Nominal clamping Ø d 7 mm	308906 7
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 6 mm	309375 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 10 mm	309002 10
ER clamping nutfor sealing rings for ER 40	309615 40
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 12 mm	309375 12
ER collet Nominal clamping Ø d 5 mm	308941 5
ER colletwith seal and spray nozzles Nominal clamping Ø d 13 mm	309002 13
ER collet HPwith seal Nominal clamping Ø d 6 mm	309377 6
ER collet Nominal clamping Ø d 9 mm	308981 9
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 11 mm	309413 11
	309448 5

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm

ER collet for machine taps with seal Nominal clamping Ø d 9 mm

309409 9

ER collet HP Nominal clamping Ø d 7 mm

309370 7

ER collet with seal Nominal clamping Ø d 8 mm

308959 8

ER collet with seal Nominal clamping Ø d 5 mm

308959 5

ER collet with seal Nominal clamping Ø d 3 mm

308959 3

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm

309447 10

ER collet HP Nominal clamping Ø d 6 mm

309368 6

ER collet HP with seal Nominal clamping Ø d 15 mm

309374 15

ER collet with seal and spray nozzles Nominal clamping Ø d 9 mm

309002 9

ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 10 mm

309413 10

ER Mini clamping nut for ER 25

309650 25

ER collet with seal Nominal clamping Ø d 22 mm

308992 22

ER collet HP Nominal clamping Ø d 6 mm

309379 6

ER collet Nominal clamping Ø d 2 mm

308878 2

ER collet for machine taps with seal Nominal clamping Ø d 6 mm

309402 6

ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm

309002 5

ER collet HP Nominal clamping Ø d 18 mm

309376 18

ER collet HP Nominal clamping Ø d 19 mm

309379 19

ER collet with seal Nominal clamping Ø d 16 mm

308992 16

ER collet Nominal clamping Ø d 1 mm

308878 1

ER collet with seal Nominal clamping Ø d 10 mm

308946 10

ER collet for machine taps with seal Nominal clamping Ø d 4 mm

309402 4

ER collet Nominal clamping Ø d 16 mm

308960 16

ER colletwith seal Nominal clamping Ø d 10 mm	308992 10
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309432 8
ER collet Nominal clamping Ø d 12 mm	308981 12
ER collet HP Nominal clamping Ø d 1 mm	309368 1
ER collet Nominal clamping Ø d 9 mm	308901 9
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 10 mm	309375 10
ER collet Nominal clamping Ø d 6 mm	309000 6
ER colletwith seal Nominal clamping Ø d 14 mm	308992 14
ER collet Nominal clamping Ø d 3 mm	308881 3
ER collet Nominal clamping Ø d 12 mm	308941 12
ER collet set HPwith seal (4; 6; 8; 10; 12; 14; 16; 20mm), 469 E	309397
ER collet set 23 pieces 4–26 mm	309320
ER collet Nominal clamping Ø d 1,5 mm	308911 1,5
ER collet HPwith seal Nominal clamping Ø d 7 mm	309377 7
ER collet Nominal clamping Ø d 16 mm	309000 16
ER clamping nutfor HiRunER collet chucks for ER 32	309617 32
ER collet Nominal clamping Ø d 2,5 mm	308941 2,5
ER collet HPwith seal Nominal clamping Ø d 12 mm	309377 12
ER clamping nutfor HiRunER collet chucks for ER 25	309617 25
ER collet for machine tapswith seal Nominal clamping Ø d 3,5 mm	309403 3,5
ER colletwith seal Nominal clamping Ø d 15 mm	308959 15
ER collet Nominal clamping Ø d 3 mm	308920 3
ER colletwith seal Nominal clamping Ø d 15 mm	309001 15
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309409 6
ER collet Nominal clamping Ø d 2 mm	308930 2
	309418 7

ER collet for machine taps with seal and spray nozzles
Nominal clamping Ø d 7 mm

ER collet Nominal clamping Ø d 2 mm	308941 2
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309447 5
ER collet Nominal clamping Ø d 8 mm	309040 8
ER collet with seal Nominal clamping Ø d 6 mm	308882 6
ER collet Nominal clamping Ø d 9 mm	308930 9
ER collet HP Nominal clamping Ø d 4 mm	309365 4
ER collet HP Nominal clamping Ø d 10 mm	309370 10
ER collet Nominal clamping Ø d 7 mm	308901 7
ER collet HP Nominal clamping Ø d 21 mm	309379 21
ER collet HP Nominal clamping Ø d 2 mm	309365 2
ER collet HP Nominal clamping Ø d 1 mm	309370 1
ER collet Nominal clamping Ø d 17 mm	309040 17
ER clamping nut for ER 20	309580 20
ER collet with seal and spray nozzles Nominal clamping Ø d 15 mm	308962 15
ER collet set 12 pieces 2–13 mm	309200
ER collet set 10 pieces 1–10 mm with seal	309164
ER collet HP Nominal clamping Ø d 25 mm	309379 25
ER collet HP Nominal clamping Ø d 8 mm	309379 8
ER collet Nominal clamping Ø d 1 mm	308911 1
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309406 4,5
ER collet with seal Nominal clamping Ø d 7 mm	308916 7
ER collet Nominal clamping Ø d 20 mm	309040 20
ER collet with seal Nominal clamping Ø d 5 mm	309001 5
ER collet HP Nominal clamping Ø d 7 mm	309376 7
ER collet HP Nominal clamping Ø d 4 mm	309379 4
	309430 7

ET collet for thread tapping, with axial compensation
Nominal clamping Ø d 7 mm

ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309406 8
---	----------

ER collet Nominal clamping Ø d 3 mm	308878 3
-------------------------------------	----------

ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309406 6
---	----------

ER collet Nominal clamping Ø d 13 mm	308960 13
--------------------------------------	-----------

ER collet HPwith seal and spray nozzles Nominal clamping Ø d 8 mm	309375 8
---	----------

ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309430 10
---	-----------

ER colletwith seal Nominal clamping Ø d 10 mm	308916 10
---	-----------

ER collet Nominal clamping Ø d 16 mm	309040 16
--------------------------------------	-----------

ER colletwith seal Nominal clamping Ø d 6 mm	308906 6
--	----------

ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309411 8
---	----------

ER colletwith seal Nominal clamping Ø d 8 mm	309001 8
--	----------

ER colletwith seal and spray nozzles Nominal clamping Ø d 8 mm	309002 8
--	----------

ER collet Nominal clamping Ø d 7 mm	308911 7
-------------------------------------	----------

ER collet Nominal clamping Ø d 15 mm	308990 15
--------------------------------------	-----------

ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309430 2,8
--	------------

ER collet Nominal clamping Ø d 9 mm	308920 9
-------------------------------------	----------

ER collet set 6 pieces, 3, 4, 5, 6, 8, 10 mmwith seal	309014
---	--------

ER collet HPwith seal and spray nozzles Nominal clamping Ø d 6 mm	309372 6
---	----------

ER collet HP Nominal clamping Ø d 24 mm	309379 24
---	-----------

ER colletwith seal and spray nozzles Nominal clamping Ø d 16 mm	308962 16
---	-----------

ER collet Nominal clamping Ø d 13 mm	308911 13
--------------------------------------	-----------

ER collet HP Nominal clamping Ø d 4 mm	309370 4
--	----------

ER collet set HP(4; 6; 8; 10; 12; 14; 16; 20mm), 470 E	309396
ER collet Nominal clamping Ø d 4 mm	308911 4
ER collet set 10 pieces 1–10 mm	309012
ER collet Nominal clamping Ø d 23 mm	308990 23
ER collet Nominal clamping Ø d 13 mm	308981 13
ER colletwith seal Nominal clamping Ø d 18 mm	308986 18
ER colletwith seal and spray nozzles Nominal clamping Ø d 3 mm	309002 3
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309411 14
ER collet Nominal clamping Ø d 13 mm	308930 13
ER collet Nominal clamping Ø d 10 mm	309000 10
ER collet HP Nominal clamping Ø d 14 mm	309379 14
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 14 mm	309413 14
ER collet Nominal clamping Ø d 5 mm	308990 5
ER collet HPwith seal Nominal clamping Ø d 4 mm	309374 4
ER collet HPwith seal Nominal clamping Ø d 6 mm	309371 6
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 16 mm	309418 16
ER collet Nominal clamping Ø d 20 mm	308990 20
ER collet Nominal clamping Ø d 15 mm	308960 15
ER colletwith seal and spray nozzles Nominal clamping Ø d 20 mm	309002 20
ER colletwith seal and spray nozzles Nominal clamping Ø d 7 mm	309002 7
ER colletwith seal Nominal clamping Ø d 6 mm	308959 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 14 mm	309002 14
ER colletwith seal and spray nozzles Nominal clamping Ø d 12 mm	308962 12
ER collet Nominal clamping Ø d 14 mm	308981 14

ER collet Nominal clamping Ø d 8 mm	308960 8
ER collet HP Nominal clamping Ø d 6 mm	309370 6
ER collet for machine tapswith seal Nominal clamping Ø d 4,5 mm	309409 4,5
ER collet HP Nominal clamping Ø d 14 mm	309373 14
ER Mini clamping nut for ER 11	309650 11
ER collet HP Nominal clamping Ø d 5 mm	309370 5
ER collet Nominal clamping Ø d 14 mm	308960 14
ER collet HP Nominal clamping Ø d 17 mm	309379 17
ER colletwith seal Nominal clamping Ø d 3 mm	308986 3
ER collet Nominal clamping Ø d 22 mm	308990 22
ER collet HP Nominal clamping Ø d 3 mm	309370 3
ER collet Nominal clamping Ø d 12 mm	308930 12
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309409 12
ER collet HPwith seal Nominal clamping Ø d 17 mm	309377 17
ER collet Nominal clamping Ø d 2 mm	308920 2
ER colletwith seal Nominal clamping Ø d 8 mm	308906 8
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 8 mm	309372 8
ER collet Nominal clamping Ø d 4 mm	308941 4
ER colletwith seal and spray nozzles Nominal clamping Ø d 11 mm	309002 11
ER clamping nut for ER 16	309580 16
ER collet HP Nominal clamping Ø d 13 mm	309379 13
ER collet set 15 pieces 2–16 mmwith seal and spray nozzles	309245
ER colletwith seal Nominal clamping Ø d 9 mm	309001 9
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 6 mm	309413 6
ER collet Nominal clamping Ø d 3,5 mm	308878 3,5
ER collet Nominal clamping Ø d 1 mm	308930 1

ER collet Nominal clamping Ø d 9 mm	308990 9
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 6 mm	309404 6
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309411 12
ER collet Nominal clamping Ø d 3 mm	308901 3
ER colletwith seal Nominal clamping Ø d 16 mm	308946 16
ER colletwith seal and spray nozzles Nominal clamping Ø d 7 mm	308962 7
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309425 4,5
ER colletwith seal and spray nozzles Nominal clamping Ø d 8 mm	308962 8
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 8 mm	309418 8
ER collet for machine tapswith seal Nominal clamping Ø d 4 mm	309403 4
ER collet Nominal clamping Ø d 8 mm	308901 8
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 11 mm	309432 11
ER collet Nominal clamping Ø d 1 mm	308881 1
ER collet Nominal clamping Ø d 4 mm	308990 4
ER colletwith seal Nominal clamping Ø d 7 mm	308921 7
ER collet Nominal clamping Ø d 26 mm	309040 26
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 6 mm	309378 6
ER collet Nominal clamping Ø d 2 mm	308911 2
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 8 mm	309448 8
ER collet Nominal clamping Ø d 11 mm	308981 11
ER colletwith seal Nominal clamping Ø d 9 mm	308906 9
ER colletwith seal Nominal clamping Ø d 10 mm	308906 10
	309414 20

ER collet for machine taps with seal Nominal clamping Ø d 20 mm

ER collet Nominal clamping Ø d 5 mm	308878 5
ER collet Nominal clamping Ø d 3 mm	308981 3
ER collet with seal Nominal clamping Ø d 12 mm	309001 12
ER collet HP with seal Nominal clamping Ø d 8 mm	309374 8
ER collet HP Nominal clamping Ø d 12 mm	309376 12
ER collet HP Nominal clamping Ø d 20 mm	309376 20
ER collet with seal Nominal clamping Ø d 4 mm	308959 4
ER collet HP with seal Nominal clamping Ø d 14 mm	309374 14
ER collet HP Nominal clamping Ø d 11 mm	309376 11
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 7 mm	309432 7
ER collet Nominal clamping Ø d 12 mm	308960 12
ER collet HP with seal and spray nozzles Nominal clamping Ø d 16 mm	309378 16
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309432 10
ER collet with seal Nominal clamping Ø d 17 mm	309001 17
ER collet Nominal clamping Ø d 16 mm	308981 16
ER collet Nominal clamping Ø d 10 mm	309040 10
ER collet HP with seal Nominal clamping Ø d 4 mm	309377 4
ER collet Nominal clamping Ø d 19 mm	309000 19
ER collet Nominal clamping Ø d 3 mm	308960 3
ER collet Nominal clamping Ø d 6 mm	309040 6