



ER mini collet holder cylindrical, for ER collet size: 20



Order data

Order number	300684 20
GTIN	4045197700841
Item class	32A

Description

Version:

Cylindrical holder with ER nut.
Through hole for internal cooling provided.

Application:

For extending the reach of side lock arbors or collet chucks.

Optional extras:

Clamping wrenches No. 309740 and No. 309745.
ER collets No. 308878 – 309434, Spare ER nuts No. 309580; 309650.

Note:

Not suitable for shrink processes.

Technical description

Clamping range	1 - 13 mm
Shank \varnothing d	20 mm
L_2	29.5 mm
Shank length L_1	140 mm
for ER collets	20 mm
External \varnothing D	28 mm
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy	HSC
Type of product	Collet chuck

Accessories

ER collet Nominal clamping Ø d 12 mm	309000 12
ER collet Nominal clamping Ø d 16 mm	308941 16
ER colletwith seal Nominal clamping Ø d 3 mm	308959 3
ER collet Nominal clamping Ø d 14 mm	308990 14
ER collet HP Nominal clamping Ø d 2 mm	309373 2
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309414 14
ER collet HP Nominal clamping Ø d 13 mm	309373 13
ER collet HP Nominal clamping Ø d 7 mm	309376 7
ER collet Nominal clamping Ø d 4 mm	308941 4
ER colletwith seal Nominal clamping Ø d 20 mm	308986 20
ER colletwith seal Nominal clamping Ø d 8 mm	308916 8
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 14 mm	309448 14
ER colletwith seal Nominal clamping Ø d 6 mm	308986 6
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309409 11
ER collet HPwith seal Nominal clamping Ø d 8 mm	309371 8
ER collet Nominal clamping Ø d 24 mm	309040 24
ER colletwith seal and spray nozzles Nominal clamping Ø d 9 mm	308922 9
ER colletwith seal Nominal clamping Ø d 11 mm	308946 11
ER colletwith seal Nominal clamping Ø d 6 mm	308959 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309445 6

ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309419 14
ER collet HPwith seal Nominal clamping Ø d 11 mm	309374 11
ER clamping nut for ER 40	309580 40
ER collet HPwith seal Nominal clamping Ø d 20 mm	309377 20
ER collet for machine tapswith seal Nominal clamping Ø d 4 mm	309402 4
ER colletwith seal Nominal clamping Ø d 8 mm	308959 8
ER colletwith seal Nominal clamping Ø d 9 mm	309001 9
ER collet Nominal clamping Ø d 1,5 mm	308911 1,5
ER collet Nominal clamping Ø d 12 mm	308930 12
ER collet Nominal clamping Ø d 6 mm	309000 6
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 6 mm	309372 6
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 4 mm	309375 4
ER collet set 8 pieces 4–16, 20 mmwith seal	309026
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 16 mm	309378 16
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309403 6
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 7 mm	309432 7
ER collet Nominal clamping Ø d 4,5 mm	308878 4,5
ER colletwith seal Nominal clamping Ø d 14 mm	308986 14
ER collet Nominal clamping Ø d 19 mm	309040 19
ER colletwith seal Nominal clamping Ø d 11 mm	308959 11
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 12 mm	309418 12
ER colletwith seal Nominal clamping Ø d 5 mm	308946 5
ER collet HP Nominal clamping Ø d 10 mm	309379 10
ER collet Nominal clamping Ø d 16 mm	308981 16

ER clamping nut for ER 32	309580 32
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2 mm	309445 2
ER colletwith seal and spray nozzles Nominal clamping Ø d 7 mm	309002 7
ER colletwith seal Nominal clamping Ø d 13 mm	308946 13
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309411 10
ER collet HP Nominal clamping Ø d 9 mm	309370 9
ER colletwith seal Nominal clamping Ø d 5 mm	309001 5
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309419 16
ER collet Nominal clamping Ø d 13 mm	309000 13
ER clamping nutHigh Speed for ER 16	309610 16
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 11 mm	309432 11
ER collet HP Nominal clamping Ø d 23 mm	309379 23
ER collet HPwith seal Nominal clamping Ø d 4 mm	309369 4
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 6 mm	309413 6
ER collet Nominal clamping Ø d 18 mm	309040 18
ER collet Nominal clamping Ø d 6 mm	308930 6
ER clamping nutHigh Speed for ER 32	309610 32
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 9 mm	309448 9
ER collet HP Nominal clamping Ø d 10 mm	309370 10
ER collet HP Nominal clamping Ø d 1 mm	309370 1
ER collet set 23 pieces 4–26 mm	309320
ER colletwith seal Nominal clamping Ø d 8 mm	308992 8
ER collet HPwith seal Nominal clamping Ø d 13 mm	309377 13
ER colletwith seal Nominal clamping Ø d 7 mm	308946 7
ER collet Nominal clamping Ø d 12 mm	308990 12

ER collet set 15 pieces 2–16 mm with seal	309244
ER collet Nominal clamping Ø d 7 mm	308990 7
ER collet Nominal clamping Ø d 2,5 mm	308901 2,5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309430 9
ER collet with seal Nominal clamping Ø d 4 mm	309001 4
ER collet with seal and spray nozzles Nominal clamping Ø d 8 mm	309002 8
ER collet Nominal clamping Ø d 5 mm	308911 5
ER collet HP Nominal clamping Ø d 16 mm	309379 16
ER collet with seal and spray nozzles Nominal clamping Ø d 7 mm	308962 7
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309403 9
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 11 mm	309448 11
ER collet HP Nominal clamping Ø d 3 mm	309379 3
ER collet Nominal clamping Ø d 3 mm	308901 3
ER collet HP Nominal clamping Ø d 19 mm	309379 19
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309447 4,5
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309416 6
ER collet Nominal clamping Ø d 3,5 mm	308881 3,5
ER plain bearing clamping nut for ER 16	309612 16
ER collet HP with seal Nominal clamping Ø d 6 mm	309374 6
ER collet with seal and spray nozzles Nominal clamping Ø d 4 mm	308922 4
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 7 mm	309448 7
ER collet with seal Nominal clamping Ø d 4 mm	308916 4
ER collet HP with seal and spray nozzles Nominal clamping Ø d 6 mm	309375 6

ER colletwith seal Nominal clamping Ø d 8 mm	308946 8
ER collet HP Nominal clamping Ø d 13 mm	309379 13
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309411 12
ER colletwith seal Nominal clamping Ø d 8 mm	309001 8
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309411 16
ER colletwith seal and spray nozzles Nominal clamping Ø d 17 mm	309002 17
ER colletwith seal Nominal clamping Ø d 8 mm	308906 8
ER collet HP Nominal clamping Ø d 14 mm	309373 14
ER collet HPwith seal Nominal clamping Ø d 6 mm	309371 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 14 mm	308962 14
ER colletwith seal Nominal clamping Ø d 6 mm	308992 6
ER collet HPwith seal Nominal clamping Ø d 17 mm	309377 17
ER colletwith seal Nominal clamping Ø d 9 mm	308986 9
ER collet Nominal clamping Ø d 26 mm	309040 26
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 12 mm	309381 12
ER collet Nominal clamping Ø d 3 mm	308920 3
ER collet Nominal clamping Ø d 7 mm	308960 7
ER collet HP Nominal clamping Ø d 3 mm	309373 3
ER collet Nominal clamping Ø d 17 mm	309040 17
ER collet Nominal clamping Ø d 1,5 mm	308878 1,5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309430 3,5
ER collet Nominal clamping Ø d 21 mm	308990 21
ER colletwith seal and spray nozzles Nominal clamping Ø d 11 mm	309002 11
ER colletwith seal Nominal clamping Ø d 3 mm	308946 3
ER collet HPwith seal Nominal clamping Ø d 19 mm	309377 19

ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309425 6
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 8 mm	309372 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 3 mm	309002 3
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309447 3,5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309432 8
ER colletwith seal Nominal clamping Ø d 13 mm	309001 13
ER collet Nominal clamping Ø d 7 mm	308911 7
ER collet Nominal clamping Ø d 5 mm	308901 5
ER collet HPwith seal Nominal clamping Ø d 6 mm	309369 6
ER collet set 10 pieces 1–10 mmwith seal and spray nozzles	309165
ER colletwith seal Nominal clamping Ø d 18 mm	308992 18
ER collet for machine tapswith seal Nominal clamping Ø d 25 mm	309419 25
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 4,5 mm	309404 4,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309447 6
ER collet Nominal clamping Ø d 11 mm	308911 11
ER colletwith seal Nominal clamping Ø d 7 mm	308916 7
ER collet HPwith seal Nominal clamping Ø d 14 mm	309374 14
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309414 7
ER colletwith seal Nominal clamping Ø d 4 mm	308986 4
ER colletwith seal Nominal clamping Ø d 14 mm	308992 14
ER colletwith seal Nominal clamping Ø d 16 mm	308946 16
ER collet Nominal clamping Ø d 9 mm	308920 9
ER collet Nominal clamping Ø d 2,5 mm	308911 2,5

ER collet Nominal clamping Ø d 14 mm	308960 14
ER colletwith seal and spray nozzles Nominal clamping Ø d 20 mm	309002 20
ER collet HP Nominal clamping Ø d 6 mm	309370 6
ER colletwith seal Nominal clamping Ø d 7 mm	308906 7
ER collet set HPwith seal (4; 6; 8; 10; 12; 14; 16; 20mm), 469 E	309397
ER collet HP Nominal clamping Ø d 15 mm	309373 15
ER collet set 15 pieces 2–16 mmwith seal and spray nozzles	309245
ER plain bearing clamping nut for ER 25	309612 25
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 11 mm	309418 11
ER collet Nominal clamping Ø d 6 mm	309040 6
ER collet HP Nominal clamping Ø d 5 mm	309376 5
ER colletwith seal Nominal clamping Ø d 3 mm	308921 3
ER collet Nominal clamping Ø d 1 mm	308901 1
ER collet Nominal clamping Ø d 9 mm	308930 9
ER collet HP Nominal clamping Ø d 6 mm	309379 6
ER collet HP Nominal clamping Ø d 1 mm	309368 1
ER collet Nominal clamping Ø d 2 mm	308960 2
ER collet Nominal clamping Ø d 6 mm	308881 6
ER colletwith seal Nominal clamping Ø d 10 mm	308946 10
ER collet Nominal clamping Ø d 4 mm	308930 4
ER collet Nominal clamping Ø d 5 mm	308918 5
ER collet Nominal clamping Ø d 5 mm	308930 5
ER collet HP Nominal clamping Ø d 16 mm	309373 16
ER collet HP Nominal clamping Ø d 24 mm	309379 24
ER collet for machine tapswith seal Nominal clamping Ø d 4,5 mm	309403 4,5
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309414 16

ER collet HP Nominal clamping Ø d 5 mm	309379 5
ER collet HP Nominal clamping Ø d 9 mm	309376 9
ER collet Nominal clamping Ø d 4 mm	308960 4
ER collet set 9 pieces 1–5 mm	309008
ER colletwith seal Nominal clamping Ø d 16 mm	308959 16
ER collet Nominal clamping Ø d 23 mm	308990 23
ER collet Nominal clamping Ø d 2 mm	308918 2
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309445 4,5
ER collet Nominal clamping Ø d 5 mm	308981 5
ER collet Nominal clamping Ø d 1,5 mm	308901 1,5
ER colletwith seal Nominal clamping Ø d 9 mm	308906 9
ER collet Nominal clamping Ø d 3 mm	308881 3
ER colletwith seal Nominal clamping Ø d 5 mm	308986 5
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309414 11
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309432 9
ER collet HPwith seal Nominal clamping Ø d 10 mm	309377 10
ER colletwith seal and spray nozzles Nominal clamping Ø d 4 mm	308962 4
ER collet set 10 pieces 1–10 mmwith seal	309164
ER collet HP Nominal clamping Ø d 4 mm	309379 4
ER collet HP Nominal clamping Ø d 6 mm	309376 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309447 3
ER colletwith seal and spray nozzles Nominal clamping Ø d 15 mm	309002 15
ER collet HP Nominal clamping Ø d 11 mm	309376 11
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 4 mm	309378 4
	309418 4,5

ER collet for machine tapswith seal and spray nozzles
Nominal clamping \varnothing d 4,5 mm

ER collet HP Nominal clamping \varnothing d 5 mm	309365 5
ER collet Nominal clamping \varnothing d 3 mm	309000 3
ER collet HP Nominal clamping \varnothing d 17 mm	309379 17
ER collet Nominal clamping \varnothing d 5 mm	308881 5
ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 3,5 mm	309445 3,5
ER collet for machine tapswith seal and spray nozzles Nominal clamping \varnothing d 14 mm	309413 14
ER collet Nominal clamping \varnothing d 5 mm	309000 5
ER collet Nominal clamping \varnothing d 1 mm	308918 1
ER colletwith seal and spray nozzles Nominal clamping \varnothing d 3 mm	308922 3
ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 5 mm	309445 5
ER colletwith seal and spray nozzles Nominal clamping \varnothing d 5 mm	309002 5
ER collet Nominal clamping \varnothing d 4 mm	309040 4
ER collet for machine tapswith seal Nominal clamping \varnothing d 6 mm	309409 6
ER clamping nutfor sealing rings for ER 40	309615 40
ER collet for machine tapswith seal Nominal clamping \varnothing d 9 mm	309414 9
ER collet for machine tapswith seal Nominal clamping \varnothing d 7 mm	309402 7
ER collet for machine tapswith seal Nominal clamping \varnothing d 4,5 mm	309414 4,5
ER colletwith seal Nominal clamping \varnothing d 20 mm	308992 20
ER collet for machine tapswith seal Nominal clamping \varnothing d 9 mm	309409 9
ER collet Nominal clamping \varnothing d 2,5 mm	308941 2,5
ER colletwith seal Nominal clamping \varnothing d 17 mm	309001 17

ER colletwith seal and spray nozzles Nominal clamping Ø d 16 mm	309002 16
ER colletwith seal Nominal clamping Ø d 3 mm	308916 3
ER clamping nut for ER 25	309580 25
ER collet Nominal clamping Ø d 22 mm	308990 22
ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309419 18
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 8 mm	309413 8
ER collet Nominal clamping Ø d 23 mm	309040 23
ER collet for machine tapswith seal Nominal clamping Ø d 20 mm	309419 20
ER collet Nominal clamping Ø d 9 mm	309040 9
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309411 7
ER collet HP Nominal clamping Ø d 25 mm	309379 25
ER collet Nominal clamping Ø d 12 mm	308960 12
ER colletwith seal Nominal clamping Ø d 11 mm	308986 11
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309448 4,5
ER collet Nominal clamping Ø d 16 mm	308990 16
ER collet HP Nominal clamping Ø d 4 mm	309368 4
ER collet HP Nominal clamping Ø d 6 mm	309368 6
ER collet HP Nominal clamping Ø d 20 mm	309376 20
ER collet HP Nominal clamping Ø d 2 mm	309376 2
ER collet Nominal clamping Ø d 6 mm	308941 6
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 20 mm	309378 20
ER colletwith seal Nominal clamping Ø d 19 mm	308986 19
ER collet Nominal clamping Ø d 15 mm	308990 15
ER collet HP Nominal clamping Ø d 19 mm	309376 19
	308962 9

ER colletwith seal and spray nozzles Nominal clamping Ø d 9 mm	
ER collet Nominal clamping Ø d 15 mm	308941 15
ER clamping nutHigh Speed for ER 40	309610 40
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309432 4,5
ER collet Nominal clamping Ø d 7 mm	308930 7
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309411 11
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309430 10
ER collet HP Nominal clamping Ø d 12 mm	309373 12
ER collet HPwith seal Nominal clamping Ø d 7 mm	309371 7
ER collet Nominal clamping Ø d 14 mm	308981 14
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309419 11
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309416 11
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309416 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 6 mm	308922 6
ER collet Nominal clamping Ø d 3 mm	308878 3
ER collet HPwith seal Nominal clamping Ø d 9 mm	309374 9
ER collet Nominal clamping Ø d 3 mm	308941 3
ER collet HPwith seal Nominal clamping Ø d 14 mm	309377 14
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309425 2,8
ER collet HP Nominal clamping Ø d 6 mm	309373 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 16 mm	308962 16
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 12 mm	309413 12

ER colletwith seal Nominal clamping Ø d 25 mm	308992 25
ER collet HPwith seal Nominal clamping Ø d 5 mm	309377 5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309449 10
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 7 mm	309404 7
ER colletwith seal Nominal clamping Ø d 12 mm	308946 12
ER collet Nominal clamping Ø d 20 mm	309000 20
ER colletwith seal Nominal clamping Ø d 8 mm	308921 8
ER collet Nominal clamping Ø d 26 mm	308990 26
ER collet HP Nominal clamping Ø d 14 mm	309379 14
ER colletwith seal Nominal clamping Ø d 15 mm	308986 15
ER collet HP Nominal clamping Ø d 9 mm	309379 9
ER colletwith seal Nominal clamping Ø d 7 mm	308986 7
ER collet HP Nominal clamping Ø d 5 mm	309373 5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309430 2,8
ER collet HPwith seal Nominal clamping Ø d 16 mm	309374 16
ER collet HPwith seal Nominal clamping Ø d 11 mm	309377 11
ER colletwith seal Nominal clamping Ø d 16 mm	308986 16
ER colletwith seal Nominal clamping Ø d 17 mm	308986 17
ER collet HP Nominal clamping Ø d 5 mm	309368 5
ER colletwith seal Nominal clamping Ø d 12 mm	308986 12
ER clamping nutfor HiRunER collet chucks for ER 32	309617 32
ER colletwith seal and spray nozzles Nominal clamping Ø d 11 mm	308962 11
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309411 6
ER collet Nominal clamping Ø d 18 mm	308981 18
ER colletwith seal Nominal clamping Ø d 4 mm	308959 4
ER colletwith seal Nominal clamping Ø d 13 mm	308959 13

ER collet Nominal clamping Ø d 10 mm	308960 10
ER colletwith seal and spray nozzles Nominal clamping Ø d 12 mm	309002 12
ER colletwith seal Nominal clamping Ø d 5 mm	308882 5
ER collet for machine tapswith seal Nominal clamping Ø d 3,5 mm	309403 3,5
ER collet HPwith seal Nominal clamping Ø d 4 mm	309374 4
ER collet Nominal clamping Ø d 4 mm	308981 4
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 7 mm	309418 7
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309403 7
ER collet Nominal clamping Ø d 10 mm	308911 10
ER collet Nominal clamping Ø d 11 mm	308960 11
ER colletwith seal Nominal clamping Ø d 6 mm	308921 6
ER Mini clamping nut for ER 25	309650 25
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 14 mm	309418 14
ER colletwith seal Nominal clamping Ø d 16 mm	309001 16
ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309414 18
ER collet HPwith seal Nominal clamping Ø d 8 mm	309377 8
ER clamping nutfor sealing rings for ER 16	309615 16
ER collet Nominal clamping Ø d 11 mm	309040 11
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 8 mm	309404 8
ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309416 18
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309402 6
ER collet HP Nominal clamping Ø d 3 mm	309368 3
ER collet HP Nominal clamping Ø d 15 mm	309376 15

ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309406 8
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 10 mm	309375 10
ER collet HP Nominal clamping Ø d 10 mm	309376 10
ER collet HPwith seal Nominal clamping Ø d 4 mm	309371 4
ER collet Nominal clamping Ø d 12 mm	308981 12
ER collet set 18 pieces 3–20 mm	309024
ER collet HP Nominal clamping Ø d 10 mm	309373 10
ER colletwith seal Nominal clamping Ø d 9 mm	308916 9
ER collet HP Nominal clamping Ø d 8 mm	309373 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 13 mm	309002 13
ER Mini clamping nut for ER 8	309650 8
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309445 4
ER colletwith seal Nominal clamping Ø d 12 mm	308992 12
ER collet HPwith seal Nominal clamping Ø d 5 mm	309371 5
ER collet Nominal clamping Ø d 3 mm	308918 3
ER colletwith seal Nominal clamping Ø d 15 mm	308959 15
ER colletwith seal Nominal clamping Ø d 16 mm	308992 16
ER collet Nominal clamping Ø d 6 mm	308920 6
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 12 mm	309432 12
ER collet HP Nominal clamping Ø d 7 mm	309368 7
ER collet Nominal clamping Ø d 5 mm	308960 5
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 12 mm	309378 12
ER collet Nominal clamping Ø d 10 mm	308920 10
ER collet Nominal clamping Ø d 11 mm	308990 11
ER collet for machine tapswith seal Nominal clamping Ø d 4 mm	309403 4

ER collet Nominal clamping Ø d 1,5 mm	308881 1,5
ER collet Nominal clamping Ø d 8 mm	308981 8
ER collet HPwith seal Nominal clamping Ø d 5 mm	309374 5
ER colletwith seal Nominal clamping Ø d 10 mm	308916 10
ER colletwith seal Nominal clamping Ø d 6 mm	308906 6
ER clamping nutfor HiRunER collet chucks for ER 16	309617 16
ER collet Nominal clamping Ø d 4 mm	308881 4
ER collet HPwith seal Nominal clamping Ø d 9 mm	309371 9
ER collet Nominal clamping Ø d 14 mm	309040 14
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309403 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 18 mm	309002 18
ER collet set 12 pieces 2–13 mm	309200
ER collet HP Nominal clamping Ø d 18 mm	309379 18
ER collet Nominal clamping Ø d 7 mm	308981 7
ER collet Nominal clamping Ø d 8 mm	308941 8
ER collet Nominal clamping Ø d 9 mm	308960 9
ER collet Nominal clamping Ø d 6 mm	308901 6
ER collet Nominal clamping Ø d 10 mm	308981 10
ER collet HPwith seal Nominal clamping Ø d 15 mm	309374 15
ER collet Nominal clamping Ø d 9 mm	308941 9
ER collet HP Nominal clamping Ø d 11 mm	309379 11
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309416 16
ER collet Nominal clamping Ø d 15 mm	308960 15
ER collet Nominal clamping Ø d 8 mm	308911 8
ER collet Nominal clamping Ø d 13 mm	308911 13
ER collet HP Nominal clamping Ø d 8 mm	309379 8
ER collet Nominal clamping Ø d 2 mm	308911 2

ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 10 mm	309413 10
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 20 mm	309418 20
ER collet Nominal clamping Ø d 17 mm	309000 17
ER collet Nominal clamping Ø d 8 mm	309000 8
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 14 mm	309378 14
ER collet HP Nominal clamping Ø d 4 mm	309373 4
ER collet Nominal clamping Ø d 6 mm	308911 6
ER colletwith seal Nominal clamping Ø d 7 mm	308921 7
ER colletwith seal Nominal clamping Ø d 5 mm	308916 5
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309416 12
ER collet HP Nominal clamping Ø d 17 mm	309376 17
ER collet Nominal clamping Ø d 22 mm	309040 22
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309414 12
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309445 3
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309414 10
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309409 10
ER colletwith seal Nominal clamping Ø d 20 mm	309001 20
ER colletwith seal Nominal clamping Ø d 10 mm	308959 10
ER colletwith seal Nominal clamping Ø d 9 mm	308959 9
ER collet Nominal clamping Ø d 8 mm	308930 8
ER collet Nominal clamping Ø d 25 mm	308990 25
ER collet HP Nominal clamping Ø d 2 mm	309365 2
ER colletwith seal Nominal clamping Ø d 5 mm	308959 5
ER collet Nominal clamping Ø d 8 mm	308960 8

ER collet HP Nominal clamping Ø d 16 mm	309376 16
ER collet Nominal clamping Ø d 15 mm	308981 15
ER collet HP Nominal clamping Ø d 4 mm	309365 4
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309432 10
ER collet Nominal clamping Ø d 4 mm	308901 4
ER plain bearing clamping nut for ER 32	309612 32
ER colletwith seal Nominal clamping Ø d 10 mm	308986 10
ER collet Nominal clamping Ø d 8 mm	308920 8
ER collet set 18 pieces 3–20 mmwith seal and spray nozzles	309285
ER collet Nominal clamping Ø d 17 mm	308981 17
ER colletwith seal Nominal clamping Ø d 6 mm	308946 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309448 5
ER collet for machine tapswith seal Nominal clamping Ø d 22 mm	309419 22
ER collet HPwith seal Nominal clamping Ø d 3 mm	309374 3
ER collet set 18 pieces 3–20 mmwith seal	309284
ER collet set 12 pieces 2–13 mm	309016
ER collet Nominal clamping Ø d 7 mm	308941 7
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309402 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 7 mm	308922 7
ER collet Nominal clamping Ø d 8 mm	308901 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 4 mm	309002 4
ER colletwith seal Nominal clamping Ø d 7 mm	309001 7
ER colletwith seal and spray nozzles Nominal clamping Ø d 10 mm	308962 10
ER collet HP Nominal clamping Ø d 15 mm	309379 15
ER collet Nominal clamping Ø d 12 mm	308941 12

ER collet Nominal clamping Ø d 2 mm	308920 2
ER colletwith seal and spray nozzles Nominal clamping Ø d 8 mm	308922 8
ER clamping nutfor sealing rings for ER 32	309615 32
ER collet Nominal clamping Ø d 13 mm	309040 13
ER collet Nominal clamping Ø d 10 mm	308990 10
ER collet Nominal clamping Ø d 19 mm	308990 19
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 6 mm	309378 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 10 mm	309002 10
ER collet Nominal clamping Ø d 4 mm	308878 4
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 9 mm	309418 9
ER collet Nominal clamping Ø d 1 mm	308911 1
ER colletwith seal Nominal clamping Ø d 4 mm	308946 4
ER colletwith seal Nominal clamping Ø d 3 mm	308906 3
ER collet Nominal clamping Ø d 9 mm	308990 9
ER collet Nominal clamping Ø d 10 mm	308930 10
ER Mini clamping nut for ER 11	309650 11
ER collet set 10 pieces 1–10 mm	309160
ER colletwith seal Nominal clamping Ø d 14 mm	308946 14
ER colletwith seal and spray nozzles Nominal clamping Ø d 14 mm	309002 14
ER collet set 7 pieces 3, 4, 5, 6, 8, 10, 12 mmwith seal	309018
ER collet Nominal clamping Ø d 1 mm	308930 1
ER collet HP Nominal clamping Ø d 8 mm	309376 8
ER collet HP Nominal clamping Ø d 21 mm	309379 21
ER collet Nominal clamping Ø d 3 mm	308930 3
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 8 mm	309375 8

ER collet HP Nominal clamping Ø d 7 mm	309379 7
ER colletwith seal Nominal clamping Ø d 3 mm	308882 3
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 12 mm	309375 12
ER collet HPwith seal Nominal clamping Ø d 13 mm	309374 13
ER colletwith seal Nominal clamping Ø d 5 mm	308906 5
ER collet HP Nominal clamping Ø d 18 mm	309376 18
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309416 7
ER collet Nominal clamping Ø d 19 mm	309000 19
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 14 mm	309375 14
ER collet Nominal clamping Ø d 3 mm	308911 3
ER collet HPwith seal Nominal clamping Ø d 7 mm	309374 7
ER colletwith seal Nominal clamping Ø d 6 mm	308882 6
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309419 10
ER collet Nominal clamping Ø d 10 mm	308941 10
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309425 3,5
ER collet Nominal clamping Ø d 18 mm	309000 18
ER collet set 6 pieces, 3, 4, 5, 6, 8, 10 mmwith seal	309014
ER colletwith seal Nominal clamping Ø d 12 mm	308916 12
ER collet Nominal clamping Ø d 20 mm	309040 20
ER colletwith seal and spray nozzles Nominal clamping Ø d 13 mm	308962 13
ER collet Nominal clamping Ø d 2 mm	308930 2
ER collet Nominal clamping Ø d 2 mm	308878 2
ER collet set HPwith seal (4; 6; 8; 10; 12; 14; 16mm) 429 E	309394
ER collet Nominal clamping Ø d 12 mm	309040 12
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 9 mm	309413 9

ER collet Nominal clamping Ø d 21 mm	309040 21
ER collet HPwith seal Nominal clamping Ø d 3 mm	309369 3
ER collet for machine tapswith seal Nominal clamping Ø d 2,8 mm	309402 2,8
ER colletwith seal Nominal clamping Ø d 8 mm	308986 8
ER collet HPwith seal Nominal clamping Ø d 12 mm	309374 12
ER collet Nominal clamping Ø d 17 mm	308990 17
ER collet HP Nominal clamping Ø d 20 mm	309379 20
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 8 mm	309418 8
ER collet Nominal clamping Ø d 5 mm	309040 5
ER collet HPwith seal Nominal clamping Ø d 4 mm	309377 4
ER colletwith seal and spray nozzles Nominal clamping Ø d 9 mm	309002 9
ER colletwith seal Nominal clamping Ø d 6 mm	308916 6
ER collet Nominal clamping Ø d 8 mm	309040 8
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 7 mm	309413 7
ER collet Nominal clamping Ø d 7 mm	308918 7
ER collet for machine tapswith seal Nominal clamping Ø d 4,5 mm	309406 4,5
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309414 8
ER colletwith seal Nominal clamping Ø d 10 mm	308992 10
ER colletwith seal and spray nozzles Nominal clamping Ø d 15 mm	308962 15
ER collet Nominal clamping Ø d 6 mm	308981 6
ER collet HP Nominal clamping Ø d 2 mm	309368 2
ER colletwith seal and spray nozzles Nominal clamping Ø d 5 mm	308922 5
ER collet Nominal clamping Ø d 7 mm	308920 7
	309378 10

ER collet HPwith seal and spray nozzles Nominal clamping Ø d 10 mm	
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309419 12
ER colletwith seal and spray nozzles Nominal clamping Ø d 12 mm	308962 12
ER collet Nominal clamping Ø d 18 mm	308990 18
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309416 10
ER colletwith seal Nominal clamping Ø d 9 mm	308921 9
ER collet for machine tapswith seal Nominal clamping Ø d 3,5 mm	309402 3,5
ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309419 9
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2,8 mm	309445 2,8
ER colletwith seal and spray nozzles Nominal clamping Ø d 3 mm	308962 3
ER colletwith seal Nominal clamping Ø d 12 mm	308959 12
ER colletwith seal Nominal clamping Ø d 10 mm	309001 10
ER collet Nominal clamping Ø d 7 mm	309000 7
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309406 10
ER collet HP Nominal clamping Ø d 7 mm	309370 7
ER collet for machine tapswith seal Nominal clamping Ø d 4 mm	309406 4
ER collet HP Nominal clamping Ø d 5 mm	309370 5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 9 mm	309447 9
ER collet Nominal clamping Ø d 13 mm	308930 13
ER collet Nominal clamping Ø d 6 mm	308960 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309448 10

ER collet Nominal clamping Ø d 9 mm	308901 9
ER collet Nominal clamping Ø d 11 mm	309000 11
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309448 4
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309409 7
ER collet Nominal clamping Ø d 2 mm	308881 2
ER collet HP with seal and spray nozzles Nominal clamping Ø d 8 mm	309378 8
ER collet HP Nominal clamping Ø d 7 mm	309373 7
ER collet set 13 pieces 1–7 mm	309010
ER collet Nominal clamping Ø d 4,5 mm	308881 4,5
ER collet with seal Nominal clamping Ø d 6 mm	309001 6
ER collet Nominal clamping Ø d 3,5 mm	308878 3,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 12 mm	309448 12
ER collet with seal and spray nozzles Nominal clamping Ø d 6 mm	309002 6
ER collet Nominal clamping Ø d 24 mm	308990 24
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309411 8
ER collet with seal Nominal clamping Ø d 13 mm	308986 13
ER collet with seal Nominal clamping Ø d 5 mm	308921 5
ER collet HP with seal Nominal clamping Ø d 9 mm	309377 9
ER collet Nominal clamping Ø d 11 mm	308981 11
ER collet Nominal clamping Ø d 14 mm	308941 14
ER collet HP Nominal clamping Ø d 3 mm	309365 3
ER collet with seal Nominal clamping Ø d 4 mm	308906 4
ER collet HP with seal Nominal clamping Ø d 10 mm	309374 10
ER Mini clamping nut for ER 20	309650 20
ER collet Nominal clamping Ø d 12 mm	308911 12

ER collet Nominal clamping Ø d 7 mm	309040 7
ER collet Nominal clamping Ø d 13 mm	308941 13
ER collet Nominal clamping Ø d 9 mm	308981 9
ER collet Nominal clamping Ø d 9 mm	308911 9
ER collet Nominal clamping Ø d 13 mm	308960 13
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309448 6
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309409 14
ER collet with seal and spray nozzles Nominal clamping Ø d 19 mm	309002 19
ER collet Nominal clamping Ø d 16 mm	309000 16
ER collet set 23 pieces 4–26 mm	309028
ER collet Nominal clamping Ø d 2,5 mm	308878 2,5
ER collet Nominal clamping Ø d 6 mm	308990 6
ER collet set 18 pieces 3–20 mm	309280
ER collet Nominal clamping Ø d 4 mm	308990 4
ER collet HP Nominal clamping Ø d 12 mm	309376 12
ER collet with seal Nominal clamping Ø d 15 mm	308946 15
ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm	308962 5
ER collet HP with seal Nominal clamping Ø d 5 mm	309369 5
ER collet HP with seal Nominal clamping Ø d 15 mm	309377 15
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 8 mm	309447 8
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309432 6
ER collet with seal Nominal clamping Ø d 18 mm	308986 18
ER collet HP Nominal clamping Ø d 12 mm	309379 12
ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309409 12
	309409 8

ER collet for machine tapswith seal Nominal clamping \varnothing d 8 mm

ER collet HP Nominal clamping \varnothing d 13 mm	309376 13
ER collet for machine tapswith seal Nominal clamping \varnothing d 4,5 mm	309411 4,5
ER clamping nutfor HiRunER collet chucks for ER 40	309617 40
ER clamping nut for ER 16	309580 16
ER collet HP Nominal clamping \varnothing d 2 mm	309370 2
ER collet HPwith seal Nominal clamping \varnothing d 10 mm	309371 10
ER collet set 10 pieces 1–10 mm	309012
ER collet Nominal clamping \varnothing d 13 mm	308990 13
ER collet Nominal clamping \varnothing d 14 mm	309000 14
ER colletwith seal Nominal clamping \varnothing d 4 mm	308921 4
ER colletwith seal Nominal clamping \varnothing d 10 mm	308921 10
ER collet Nominal clamping \varnothing d 4 mm	309000 4
ER collet HPwith seal Nominal clamping \varnothing d 7 mm	309377 7
ER colletwith seal Nominal clamping \varnothing d 3 mm	309001 3
ER collet for machine tapswith seal Nominal clamping \varnothing d 14 mm	309411 14
ER collet Nominal clamping \varnothing d 10 mm	308901 10
ER colletwith seal Nominal clamping \varnothing d 4 mm	308882 4
ER colletwith seal Nominal clamping \varnothing d 22 mm	308992 22
ET collet for thread tapping, with axial compensation Nominal clamping \varnothing d 7 mm	309430 7
ER collet Nominal clamping \varnothing d 11 mm	308941 11
ER collet Nominal clamping \varnothing d 15 mm	309040 15
ER collet for machine tapswith seal and spray nozzles Nominal clamping \varnothing d 6 mm	309404 6
ER collet for machine tapswith seal and spray nozzles Nominal clamping \varnothing d 18 mm	309418 18
ER collet Nominal clamping \varnothing d 3 mm	308981 3

ER collet HPwith seal Nominal clamping Ø d 8 mm	309374 8
ER collet set 15 pieces 2–16 mm	309240
ER collet Nominal clamping Ø d 9 mm	309000 9
ER collet set HPwith seal (3; 4; 5; 6; 8; 10mm), 425 E	309391
ER collet HP Nominal clamping Ø d 8 mm	309370 8
ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309411 9
ER collet HP Nominal clamping Ø d 14 mm	309376 14
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309430 6
ER collet HP Nominal clamping Ø d 3 mm	309370 3
ER collet Nominal clamping Ø d 7 mm	308901 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309447 5
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 16 mm	309418 16
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309406 7
ER collet set HP(4; 6; 8; 10; 12; 14; 16; 20mm), 470 E	309396
ER collet Nominal clamping Ø d 16 mm	309040 16
ER collet HP Nominal clamping Ø d 11 mm	309373 11
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309406 6
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 6 mm	309418 6
ER colletwith seal Nominal clamping Ø d 12 mm	309001 12
ER collet HP Nominal clamping Ø d 4 mm	309376 4
ER collet Nominal clamping Ø d 4 mm	308918 4
ER collet for machine tapswith seal Nominal clamping Ø d 20 mm	309414 20
ER collet set HP(3; 4; 5; 6; 8; 10mm), 426 E	309390
	309402 9

ER collet for machine taps with seal Nominal clamping \varnothing d 9 mm

ER collet Nominal clamping \varnothing d 3 mm 308960 3

ER collet for machine taps with seal Nominal clamping \varnothing d 4,5 mm 309402 4,5

ER collet Nominal clamping \varnothing d 1 mm 308920 1

ER collet for machine taps with seal Nominal clamping \varnothing d 6 mm 309419 6

ER collet with seal and spray nozzles Nominal clamping \varnothing d 8 mm 308962 8

ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 10 mm 309447 10

ER collet with seal Nominal clamping \varnothing d 9 mm 308946 9

ER clamping nut for ER 20 309580 20

ER collet with seal Nominal clamping \varnothing d 11 mm 309001 11

ER collet for machine taps with seal Nominal clamping \varnothing d 9 mm 309406 9

ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 4 mm 309447 4

ER collet Nominal clamping \varnothing d 20 mm 308990 20

ET collet for thread tapping, with axial compensation Nominal clamping \varnothing d 4,5 mm 309425 4,5

ER collet HP with seal and spray nozzles Nominal clamping \varnothing d 4 mm 309372 4

ER collet for machine taps with seal Nominal clamping \varnothing d 2,8 mm 309403 2,8

ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 3,5 mm 309404 3,5

ER collet Nominal clamping \varnothing d 25 mm 309040 25

ER collet HP Nominal clamping \varnothing d 22 mm 309379 22

ER collet HP with seal Nominal clamping \varnothing d 12 mm 309377 12

ER collet for machine taps with seal Nominal clamping \varnothing d 4,5 mm 309416 4,5

ER Mini clamping nut for ER 16	309650 16
ER collet Nominal clamping Ø d 10 mm	309000 10
ER collet HPwith seal Nominal clamping Ø d 3 mm	309377 3
ER collet set 7 pieces 4–16 mmwith seal	309022
ER collet HP Nominal clamping Ø d 4 mm	309370 4
ER collet Nominal clamping Ø d 2 mm	308901 2
ER colletwith seal Nominal clamping Ø d 3 mm	308986 3
ER collet Nominal clamping Ø d 4 mm	308911 4
ER collet for machine tapswith seal Nominal clamping Ø d 3,5 mm	309406 3,5
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309419 8
ER collet set 7 pieces 1–7 mm	309155
ER collet Nominal clamping Ø d 6,5 mm	308881 6,5
ER collet Nominal clamping Ø d 10 mm	309040 10
ER clamping nutfor HiRunER collet chucks for ER 25	309617 25
ER collet Nominal clamping Ø d 4 mm	308920 4
ER colletwith seal Nominal clamping Ø d 14 mm	309001 14
ER collet Nominal clamping Ø d 8 mm	308990 8
ER collet Nominal clamping Ø d 16 mm	308960 16
ER collet for machine tapswith seal and spray nozzles Nominal clamping Ø d 4,5 mm	309413 4,5
ER plain bearing clamping nut for ER 40	309612 40
ER collet Nominal clamping Ø d 1 mm	308881 1
ER collet Nominal clamping Ø d 13 mm	308981 13
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309419 7
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309414 6
ER collet HP Nominal clamping Ø d 1 mm	309365 1
	309416 20

ER collet for machine taps with seal Nominal clamping \varnothing d 20 mm

ER collet Nominal clamping \varnothing d 2,5 mm	308881 2,5
ER collet Nominal clamping \varnothing d 1 mm	308878 1
ER collet Nominal clamping \varnothing d 11 mm	308930 11
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 10 mm	309418 10
ER collet Nominal clamping \varnothing d 5 mm	308920 5
ER collet for machine taps with seal Nominal clamping \varnothing d 4,5 mm	309409 4,5
ER collet HP with seal and spray nozzles Nominal clamping \varnothing d 18 mm	309378 18
ER collet HP Nominal clamping \varnothing d 26 mm	309379 26
ER collet HP with seal Nominal clamping \varnothing d 6 mm	309377 6
ER collet with seal and spray nozzles Nominal clamping \varnothing d 10 mm	308922 10
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 11 mm	309413 11
ER collet with seal Nominal clamping \varnothing d 10 mm	308906 10
ET collet with radial compensation for tapping and reaming Nominal clamping \varnothing d 7 mm	309447 7
ER collet with seal Nominal clamping \varnothing d 18 mm	309001 18
ER collet for machine taps with seal Nominal clamping \varnothing d 9 mm	309416 9
ER collet with seal Nominal clamping \varnothing d 11 mm	308916 11
ER collet Nominal clamping \varnothing d 5 mm	308990 5
ER collet for machine taps with seal Nominal clamping \varnothing d 16 mm	309409 16
ER collet Nominal clamping \varnothing d 2 mm	308941 2
ER collet HP with seal Nominal clamping \varnothing d 16 mm	309377 16
ER collet Nominal clamping \varnothing d 5 mm	308941 5
ER collet HP with seal Nominal clamping \varnothing d 18 mm	309377 18

ER collet HPwith seal Nominal clamping Ø d 3 mm	309371 3
ER colletwith seal Nominal clamping Ø d 7 mm	308959 7
ER collet Nominal clamping Ø d 19 mm	308981 19
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309430 8
ER collet Nominal clamping Ø d 20 mm	308981 20
ER collet Nominal clamping Ø d 15 mm	309000 15
ER colletwith seal and spray nozzles Nominal clamping Ø d 6 mm	308962 6
ER collet Nominal clamping Ø d 5 mm	308878 5
ER collet Nominal clamping Ø d 6 mm	308918 6
ER collet Nominal clamping Ø d 5,5 mm	308881 5,5
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309416 14
ER clamping nutfor sealing rings for ER 25	309615 25
ER colletwith seal Nominal clamping Ø d 19 mm	309001 19
ER collet HP Nominal clamping Ø d 3 mm	309376 3
ER collet Nominal clamping Ø d 7 mm	308881 7
ER collet HP Nominal clamping Ø d 9 mm	309373 9
ER clamping nutHigh Speed for ER 25	309610 25
ER colletwith seal Nominal clamping Ø d 14 mm	308959 14
ER colletwith seal Nominal clamping Ø d 15 mm	309001 15
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 8 mm	309448 8
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309430 4,5