

Garant

Clamping toolholder SRDCN 30°, for indexable inserts RC.X, neutral, Shank / insert size: 12/06mm



Order data

Order number	260611 12/06
GTIN	4062406059316
Item class	21T

Technical description

suitable indexable insert	RC.T 0602
Shank size	12 mm
Insert size	6 mm
ISO code toolholder	SRDCN 1212F06
Overhang L ₁ neutral holders	12.4 mm
Overall length L neutral holders	80 mm
Pack of insert screws	269028 15
Functional width L ₄ neutral holders	9 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 15	269028 15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8