

Garant

Clamping toolholder SRDCN 30°, for indexable inserts RC.X, neutral, Shank / insert size: 16/06mm



Order data

Order number	260611 16/06
GTIN	4062406059323
Item class	21T

Technical description

Shank size	16 mm
Functional width L ₄ neutral holders	11 mm
Overhang L ₁ neutral holders	12.4 mm
Overall length L neutral holders	100 mm
Pack of insert screws	269028 15
ISO code toolholder	SRDCN 1616H06
suitable indexable insert	RC.T 0602
Insert size	6 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 15	269028 15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8