

Garant
Clamping toolholder SRDCN 30°, for indexable inserts RC.X, neutral, Shank / insert size: 20/08mm

Order data

Order number	260611 20/08
GTIN	4062406059361
Item class	21T

Technical description

Shank size	20 mm
suitable indexable insert	RC.T 0803
Pack of insert screws	269028 29
ISO code toolholder	SRDCN 2020K08
Overall length L neutral holders	125 mm
Overhang L ₁ neutral holders	16.4 mm
Insert size	8 mm
Functional width L ₄ neutral holders	14 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

