

**Garant**

**Clamping toolholder SRDCN 30°, for indexable inserts RC.X, neutral, Shank / insert size: 20/06mm**



## Order data

Order number	260611 20/06
GTIN	4062406059330
Item class	21T

## Technical description

Insert size	6 mm
Functional width L <sub>4</sub> neutral holders	13 mm
Overhang L <sub>1</sub> neutral holders	12.4 mm
Pack of insert screws	269028 15
ISO code toolholder	SRDCN 2020K06
Overall length L neutral holders	125 mm
Shank size	20 mm
suitable indexable insert	RC.T 0602
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

**Accessories**

Set of insert screws Type 15	269028 15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8