

**Garant**
**Socket set 3/8 inch square drive 15 pieces, Type: 6**

**Order data**

Order number	633812 6
GTIN	4062406060718
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120**.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay**. With hexagon sockets No. 637229.

**Application:**

For hexagon head screws / nuts with thread M5 – M12.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

Sockets: 11 pcs.

size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19 mm

Extensions: 2 pcs. No. 635429 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Storage in: ABS plastic box

**Technical description**

Drive profile	Hexagon socket
Width across flats range, hexagon sockets	8-19 mm

Square drive	3/8 in
Material	Chromium vanadium
Packaging	ABS plastic box
Length	257 mm
Width	147 mm
Height	45 mm
Surface	chrome-plated
Degree of fill of a drawer in units	5×10
Type of product	Socket spanner

---

## Accessories

Extension, 3/8 inch overall length 75 mm	635429 75
PUR foam inlay for set 633812	630304 633812
Universal joint, 3/8 inch Type 3/8	636229 3/8
Reversible ratchet, 3/8 inch with ejector Type	635025
Extension, 3/8 inch overall length 240 mm	635429 240
Modular box Type 2	630305 2