

**Garant**
**Bi-hexagon socket, 1/2 inch, Width across flats: 30mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 642129 30     |
| GTIN         | 4062406061685 |
| Item class   | 61A           |

**Description**
**Version:**

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Close tolerance internal square for secure fit on the tool. Square socket drives to **DIN 3120**.

**Close tolerance widths across flats** protects nuts and bolt heads. **Thin walls** for access to restricted places. Bi-hexagon (double hexagon) with **HT Drive** profile that protects the corners of nuts and bolt heads.

**Standard:**
**DIN 3124**
**Material:**

Chrome vanadium steel, chrome-plated.

**Note:**

GARANT and HOLEX bi-hex sockets including are available also in imperial sizes from our eShop (GARANT: No. 642132; HOLEX: No. 642122).

Square drive: 1/2 in

Ø drive output end: 39.8 mm

Length: 44 mm

**Technical description**

|                    |       |
|--------------------|-------|
| Length             | 44 mm |
| Width across flats | 30 mm |

|                    |                       |
|--------------------|-----------------------|
| Ø drive output end | 39.8 mm               |
| Square drive       | 1/2 in                |
| Standard           | DIN 3124              |
| Drive profile      | Bi-hex socket         |
| Material           | Chrome vanadium steel |
| Surface            | chrome-plated         |
| Type of product    | Socket insert         |