

Garant

Clamping toolholder PSKNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 40/19mm



Order data

Order number	251111 40/19
GTIN	4062406063160
Item class	21T

Technical description

Shank size	40 mm
Shim pins pack	259044 1
Functional width L ₄	50 mm
Lever screw	259018 1
Overall length L	250 mm
Shim	259031 16
Head length L ₁	45 mm
ISO code toolholder	PSKNR/L 4040S19
Insert size	19 mm
Lever	259015 1
suitable indexable insert	SN.. 1906..
Shim punches pack	259047 1
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar