

Garant
**Clamping toolholder PSKNR 75°, for indexable inserts SN., right-hand,
Shank / insert size: 40/19mm**

Order data

Order number	251110 40/19
GTIN	4062406063153
Item class	21T

Technical description

Shim pins pack	259044 1
suitable indexable insert	SN.. 1906..
Shim punches pack	259047 1
Shim	259031 16
Head length L ₁	45 mm
Functional width L ₄	50 mm
Shank size	40 mm
Lever screw	259018 1
Overall length L	250 mm
ISO code toolholder	PSKNR/L 4040S19
Lever	259015 1
Insert size	19 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar