

Garant
Clamping toolholder PSDNN 45°, for indexable inserts SN., neutral, Shank / insert size: 20/12mm

Order data

Order number	251114 20/12
GTIN	4062406063207
Item class	21T

Technical description

Shim pins pack	259044 2
suitable indexable insert	SN.. 1204..
Shim	259031 20
Shank size	20 mm
Functional width L ₄ neutral holders	10.3 mm
Overhang L ₁ neutral holders	28 mm
Lever screw	259018 2
Lever	259015 2
Overall length L neutral holders	125 mm
ISO code toolholder	PSDNN 2020K12
Insert size	12 mm
Shim punches pack	259047 2
Standard	Works standard
Application type	neutral
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar