

Garant
Clamping toolholder PSDNN 45°, for indexable inserts SN., neutral, Shank / insert size: 16/12mm

Order data

| | |
|--------------|---------------|
| Order number | 251114 16/12 |
| GTIN | 4062406063191 |
| Item class | 21T |

Technical description

| | |
|---|----------------|
| Lever | 259015 2 |
| Shim pins pack | 259044 2 |
| Shank size | 16 mm |
| suitable indexable insert | SN.. 1204.. |
| Lever screw | 259018 2 |
| Overall length L neutral holders | 100 mm |
| Shim punches pack | 259047 2 |
| Functional width L ₄ neutral holders | 8.3 mm |
| Overhang L ₁ neutral holders | 31 mm |
| ISO code toolholder | PSDNN 1616H12 |
| Insert size | 12 mm |
| Shim | 259031 20 |
| Standard | Works standard |
| Application type | neutral |
| Through-coolant | no |

| | |
|------------------------|-------------------------------|
| Setting angle κ | 45 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |