

**Garant**

**Clamping toolholder PSDNN 45°, for indexable inserts SN., neutral, Shank / insert size: 25/12mm**



## Order data

Order number	251114 25/12
GTIN	4062406063214
Item class	21T

## Technical description

Functional width L <sub>4</sub> neutral holders	12.8 mm
Insert size	12 mm
ISO code toolholder	PSDNN 2525M12
Lever	259015 2
suitable indexable insert	SN.. 1204..
Overall length L neutral holders	150 mm
Lever screw	259018 2
Shim	259031 20
Shank size	25 mm
Shim pins pack	259044 2
Overhang L <sub>1</sub> neutral holders	29 mm
Shim punches pack	259047 2
Standard	Works standard
Application type	neutral
Through-coolant	no

Setting angle $\kappa$	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar