

Garant

Steel boring bar A.. SDXCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 10/04mm


Order data

Order number	260344 10/04
GTIN	4062406066741
Item class	21T

Technical description

Setting angle κ	93 degrees
Pack of insert screws	269028 26
Overall length L	100 mm
Insert size	4 mm
ISO code toolholder	A10H SDXCR/L04
Head length L_1	22 mm
suitable indexable insert	DC.. 04T0..
Centre offset L_3	7 mm
Clamping height L_2	9 mm
Minimum pre-drill $\varnothing D_{min}$	12.5 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5