

**Adjustable spanner, overall length: 450mm****Order data**

| | |
|--------------|---------------|
| Order number | 814001 450 |
| GTIN | 4062406072100 |
| Item class | 82A |

Description**Version:**

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

Adjustable spanner, chrome-plated.

Technical description

| | |
|----------------------------|--------------------------|
| overall length | 18 in |
| maximum width across flats | 55 mm |
| Jaw position | 22 degrees |
| Manufacturing process | drop-forged and hardened |
| non-sparking | no |
| Scaling | yes |
| Grips | no |
| Type of product | Adjustable spanners |