



Boring bar set, steel, without IC, right-hand, Type: SET07



Order data

Order number	260348 SET07
GTIN	4062406074982
Item class	29W

Description

Version:

Without through-coolant feed.

Supplied with:

Plastic case

Technical description

suitable indexable insert	DC..0702..
ISO code toolholder	S0810H SDUCR07; S1012K SDUCR07; S1216M SDUCR07
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{min}$	12 mm
Minimum pre-drill $\varnothing D_{min}$	15.5 mm
Minimum pre-drill $\varnothing D_{min}$	19 mm
Clamping height L_2	9 mm

Clamping height L ₂	11 mm
Clamping height L ₂	15 mm
Centre offset L ₃	6.5 mm
Centre offset L ₃	9 mm
Centre offset L ₃	11 mm
Head length L ₁	22.5 mm
Head length L ₁	27.5 mm
Head length L ₁	40.5 mm
Overall length L	100 mm
Overall length L	125 mm
Overall length L	150 mm
Neck width L ₄	8 mm
Neck width L ₄	10 mm
Neck width L ₄	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Type of product	Boring bar