



## Husqvarna K 1 PACE Rescue

K 1 PACE Rescue high power battery cutter has the power and performance you expect from equivalent petrol-powered cutters. Equipped with X-Halt™ brake function for operational safety and a magnesium blade guard designed to be visible in smoke and water spray for ease of use. Low vibrations and optimally balanced machine ensures easier operation. Powered by Husqvarna PACE battery system with high power and fast charging and a well-suited match with our specially designed battery blade range for maximised cutting depth and optimised performance.



### Powerful

Power and performance in par with equivalent petrol-powered cutters. With an integrated gearbox for higher torque. For high productivity.



### Adjustable carry strap

Adjustable carry strap allows full freedom of movement.

### Magnesium blade guard

With decreased weight and reflective decals for high visibility in smoke and water spray, which enhances control of the cutter



### Safe operation

X-Halt™ blade brake function capable of stopping the rotation of the blade in fractions of a second.



## PXM\_FEATURES

- Magnesium blade guard
- Adjustable carry strap allows full freedom of movement.
- Powerful
- Safe operation
- Zero direct emission
- Flexible
- A more sustainable choice
- Ergonomic and user-friendly
- High power PACE battery system
- Built-in connectivity
- Smart battery placement
- In-house developed brushless motor provides a high and consistent torque.
- Perfect balance
- Ergonomic handles
- Easy to change bladeguard position
- Our anti-vibration system reduces vibrations in the cutter handles, so they are more comfortable to hold and can be used for longer periods. To provide the user a comfortable operating position and to reduce strain, the distance between the handles is large. The handles and the short engine body mean the user always stands close to the machine, for easier handling and control.

### Technical Specifications

CAPACITY	
Output shaft RPM, max	3400 rpm
Peripheral speed, max	11600 fpm
Water pressure, max	87 psi
DIMENSIONS	
Article gross weight	9400 g
Article net weight	7500 g
Arbor diameter	0.8/1 in
Blade diameter, max	14.21 in
Blade flange diameter	2.36 in
Cutting depth, max	5.7 in
Product size height	16.65 in
Product size length	26.1 in
Product size width	9.17 in
Weight	17.42 lbs
ENGINE	
Engine cooling	Fan/Air
EQUIPMENT	
Water connector	Gardena Male
LUBRICANTS	
Engine cooling	Fan/Air
SOUND AND NOISE	
Sound power level, measured	112.9 dB(A)
Sound pressure level at operators ear	101.9 dB(A)
VIBRATIONS	
Daily Vibration Exposure (A8)	0.9 m/s <sup>2</sup>
Vibrations left/front handle	2.2 m/s <sup>2</sup>
Vibrations right/rear handle	1.2 m/s <sup>2</sup>
PACKAGING	
Packaging length	723 mm
Packaging width	261 mm
Packaging height	460 mm
Packaging volume	86.8 dm <sup>3</sup>

## ACCESSORIES



HUSQVARNA WT 151  
599 58 23-04



HUSQVARNA WT 151  
599 58 24-06



HUSQVARNA B380X PACE  
970 49 41-02



HUSQVARNA B750X PACE  
970 49 42-02



HUSQVARNA C900X PACE  
970 49 50-03



VAC ATTACHMENT  
529 57 79-01



BATTERY TRANSPORTATION BOX  
531 21 54-02



HUSQVARNA WL 81  
970 58 49-01



HUSQVARNA WL 81  
970 61 73-01