



## LED workplace light with adjustable arm

<b>Product-Nr.</b>	121012-02
<b>EAN:</b>	4260556623726
<b>Model:</b>	CENALED SPOT Gelenkarm
<b>Order number:</b>	121012-02
<b>Model:</b>	CENALED SPOT Gelenkarm
<b>Type:</b>	LED workplace light with adjustable arm
<b>Illuminant:</b>	High Power LED
<b>Power consumption:</b>	~8,5 W
<b>Lamp luminous flux:</b>	1120 lm
<b>Lamp luminous efficiency:</b>	134 lm/W
<b>Light distribution:</b>	direct
<b>Light colour:</b>	5000K 3-step MacAdam
<b>Connected load:</b>	24V DC $\pm$ 10%
<b>Power supply:</b>	-
<b>Connection (connector):</b>	Connection cable, oil flex, with open cable ends
<b>Degree of protection:</b>	IP67
<b>Class of protection:</b>	III
<b>Beam angle (optics):</b>	30°
<b>Operating temperature:</b>	-10 °C -> +50 °C (14 °F -> 122 °F)
<b>Colour rendering (Ra):</b>	>80
<b>Lamps lifetime:</b>	> 60.000 h (L80/B10)
<b>Housing material:</b>	aluminium (powder finished)
<b>Cover material:</b>	safety glass, shatterproof
<b>Length articulated arms:</b>	350 mm / 400 mm
<b>base height:</b>	59 mm (2,32")
<b>Weight (net):</b>	1350 g (~48 oz)
<b>Gross weight:</b>	2550 g (~90 oz)
<b>Risk group (DIN EN 62471):</b>	free group
<b>Markings:</b>	CE, UKCA, ETL Listed (5003529)
<b>Dimmable:</b>	yes, via push button at the light head, ON/OFF and dimming
<b>Mounting accessories:</b>	magnet holder plate optional
<b>Made in:</b>	Germany
<b>Feature:</b>	universal workplace light with high protection degree

Abstand d=50 cm  
 $E_{1000} = 3114$  lux  
 $E_{2000} = 8584$  lux  
 $E_{3000} = 516$  lux

