


Plug



Product-Nr.	200200-04
EAN:	4260556622002
Model:	Zubehör Anschluss
Insulation resistance (MOhm):	> 100
Order number:	200200-04
Model:	Zubehör Anschluss
Type:	Plug
Coding:	A-coded
Amount:	1 piece
Suitable for:	24 V DC LED lights with M12 plug, A-type coded
Tipo di connessione:	screwed
Cable passage:	4 mm -> 6 mm (~0,16" -> ~0,24")
Wire cross-section:	0,25 mm ² ... 0,75 mm ²
Cable box material:	Plastic
Material:	Throw: CuZn, nickel-plated; Contacts: CuZn, CuSnZn; Cable box: plastic
AWG wire cross-section:	24 - 18
Type:	straight
Nominal voltage:	250 V AC/DC
Operating voltage:	24V DC
Current load:	4 A
Ambient temperature:	-40°C -> +80 °C (-40 °F -> 176 °F)
Passage resistance (ohms):	< 8
Insulation resistance (Ohm):	>= 100 Mio.
UL:	No
Protection class (mounting):	IP67
Cover material:	CuZn, nickel-plated
Contact material:	CuZn, CuSnZn
Weight (net):	50 g (~2 oz)
Gross weight:	100 g (~4 oz)
Note:	assemblable