



M8 socket to M12



<b>Product-Nr.</b>	200200-21
<b>EAN:</b>	4260556626192
<b>Model:</b>	M8 Steckverbinder
<b>Order number:</b>	200200-21
<b>Model:</b>	M8 Steckverbinder
<b>Type:</b>	M8 socket to M12
<b>Coding:</b>	A-coded
<b>Amount:</b>	1 piece
<b>Suitable for:</b>	TUBELED_25 (not TUBELED_25 RGB-W)
<b>Tipo di connessione:</b>	screw-fastened
<b>Number of poles:</b>	3
<b>Material:</b>	Contact carrier: plastic, TPU, BK; Overlay: metal, CuZn, nickel-plated; Seal: FPM/FKM; Contacts: metal, CuZn, gold-plated
<b>Mechanical life:</b>	>100 mating cycles
<b>Ambient temperature:</b>	-30°C -> +90 °C (-22 °F -> 194 °F)
<b>Insulation resistance (Ohm):</b>	>= 100 Mio.
<b>Handle body material:</b>	Plastic, TPU, BK
<b>Contact carrier material:</b>	Plastic, TPU, BK
<b>Cover material:</b>	Metal, CuZn, nickel-plated
<b>Contact material:</b>	Metal, CuZn, gold-plated
<b>Weight (net):</b>	100 g (~4 oz)
<b>Gross weight:</b>	100 g (~4 oz)