




Sensor cable, TPE, grey



Product-Nr.	201100-01
EAN:	4260556622576
Model:	Sensor Kabel, M12 Buchsen 4-Polig F&B
Order number:	201100-01
Model:	Sensor Kabel, M12 Buchsen 4-Polig F&B
Type:	Sensor cable, TPE, grey
Coding:	A-coded
Amount:	1 piece
Suitable for:	LED2WORK lights 24V DC, except for RGB and RGB-W luminaire
Cable length:	5 m (~16,4 ft.)
Attachment to a luminaire:	Connector socket M12, straight, EPDM seal, V4A cap nut
Cable ends:	M12 plug, straight / M12 socket, straight
Number of poles:	4
Material:	Contact carrier: plastic, PP, GY; Coupling: stainless steel, V4A; Seal: EPDM; Contacts: metal, CuSn, gold-plated
Nominal voltage:	250V
Current load per PIN:	4000 mA
Ambient temperature:	-40°C -> +105 °C (-40 °F -> 221 °F)
Passage resistance (ohms):	< 0,005
Insulation resistance (Ohm):	>= 100 Mio.
RoHS Directive:	Yes
UL:	Yes
Protection class (mounting):	IP65, IP67, IP68
Cable material:	TPE
Handle body material:	Plastic, PP, GY
Contact carrier material:	Plastic, PP, GY
Cover material:	Stainless steel, V4A
Sealing material:	EPDM
Contact material:	Metal, CuSn, gold-plated
Standards:	IEC 61076-2-101
Weight (net):	200 g (~7 oz)
Gross weight:	250 g (~9 oz)
Feature:	Suitable for food and beverages, FDA-approved