



sensor cable, TPE, gray

<b>Product-Nr.</b>	201100-10
<b>EAN:</b>	4260556625980
<b>Model:</b>	Sensor Kabel, offen/M12 Buchse 5-Polig F&B

Order number:	201100-10
<b>Model:</b>	Sensor Kabel, offen/M12 Buchse 5-Polig F&B
Type:	sensor cable, TPE, gray
<b>Coding:</b>	A-coded
Amount:	1 piece
<b>Suitable for:</b>	LED2WORK 24V DC luminaires, esp. for RGB and RGB-W lights
Cable length:	5 m (~16,4 ft.)
<b>Attachment to a luminaire:</b>	connector M12 socket, straight, seal EPDM, cap stainless steel
Cable ends:	open ends, 5 cores / M12 socket, straight
<b>Number of poles:</b>	5

<b>Material:</b>	Contact carrier: plastic, PP, GY; Coupling: stainless steel, V4A; Seal: EPDM; Contacts: metal, CuSn, gold-plated
<b>Ambient temperature:</b>	-40°C -> +105 °C (-40 °F -> 221 °F)
Handle body material:	plastics, PP, GY
<b>Contact carrier material:</b>	plastics, PP, GY
Cover material:	stainless steel V4A
<b>Contact material:</b>	metal, CuSn, gold-plated
Weight (net):	200 g (~7 oz)
<b>Gross weight:</b>	250 g (~9 oz)
<b>Feature:</b>	especially suitable for Food+Beverage, FDA approved

1	BN
2	WH
3	BU
4	BK
5	GN YE

