

Project:

Type:

Prepared By:

Date:



UPC: 019813749556



### Features and Benefits

Produces rich and vibrant colors >90CRI

Energy efficient replacement for incandescent and halogen PAR lamps

Constructed from durable materials which lowers risk of breakage

Rated for use in enclosed and open fixtures in dry and damp locations\*

Single optic and full face lens for precise beam angle control

Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs

Title 20 Compliant, UL Listed

Dimmable down to 10% (check dimmer compatibility list)

\*PAR38 is wet rated

## Technical Specifications

### Performance

#### Product Type:

PAR

#### Input Wattage:

11W

#### Lumens (Nominal):

900lm

#### Efficacy:

82 lm/W

#### L70 Lifespan:

25,000-Hour LED lifespan based on IES LM-70 results

#### Wattage Equivalency:

75W

### LED Characteristics

#### Color Accuracy (CRI):

90 CRI

#### Color Temperature:

4000K

### Electrical

#### Power Factor:

>0.9

#### Dimmable:

Yes, down to 10%

#### Input Voltage:

120V

#### Operating Temperature:

-20°C - 40°C

### Construction

#### Bulb Shape:

PAR30S

#### Enclosure Material:

Plastic

#### Housing Finish:

White

#### Base Type:

E26

### Optical

#### Beam Angle:

40°

## Technical Specifications (continued)

## Optical

## MBCP:

1315

## Other

## Technology EQ:

Halogen

## Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of three (3) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at [rablighting.com/warranty](http://rablighting.com/warranty).

## Compliance

## UL Listed:

Yes

## Environment/Fixture Rating:

Damp / Enclosed

## T20 Compliant:

Yes, Title 20 Tier 2

## T24 JA8 Compliant:

Complies with Title 24 Appendix JA8

## RoHS:

Mercury and UV free. RoHS-compliant components.

## FCC:

Complies with Part 15 of the FCC Rules


## Model Number:

P10013(PAR30S-11-940-40D-DIM)

## Case and Pallet Dimensions

|        | QTY | LENGTH (in) | WIDTH (in) | HEIGHT (in) |
|--------|-----|-------------|------------|-------------|
| CASE   | 6   | 12.8        | 8.5        | 4.7         |
| PALLET | 864 | 46.7        | 38.4       | 37.8        |

## Dimension



Light Distribution

