



We asked, you answered and we listened.

When we asked you how we could improve our N-series of cartridges and filters, we listened to you. You needed better visibility, less bulk, easier fit checks, and minimal breathing resistance – without sacrificing service life. We love a challenge!

We have redesigned our North cartridges and cartridge filter combinations from top to bottom. We started with the profile and shaved off 7%. What does 7% mean? Expanded field of vision, more productivity, less bulk and less worker fatigue. We redesigned the inhalation ports and made it easier than ever to perform user seal checks. Then we took the edge off the top of our combo to reduce chances of snagging and catching in tight and crowded work areas.

What did we keep? Everything you like about our cartridges. Same long service life and threaded connectors that fit North half masks and full facepieces. Same great reliability you have come to know and trust from North products.

FEATURES AND BENEFITS

- Lower profile so cartridges don't intrude into the work zone
 - *See everything you need to see, even when doing close up detail work*
- Easy user seal check
 - *Even with the smallest, most petite hands, you can achieve an easy user seal check. No struggling or using adapters to achieve a negative check*
- Curved edge on P100 filter combination
 - *No catching, no snagging on pipes or other workplace hazards*
- Threaded connectors that fit North half masks and full facepieces
 - *Backwards compatible with current 5500, 7700, 5400 and 7600 Series facepieces. Easy to attach – won't come off accidentally*
- Same long service life
 - *Get the job done without frequent change outs*
- Full offering, from organic vapors to multi-contaminant
 - *Select the right cartridges for your job*



North Air-Purifying Cartridges and Filters

**N75001L****N75002L****N75003L****N75004L****N750052L****75SCL****7581P100L****7582P100L****7583P100L****7584P100L****75852P100L****75SCP100L**

ORDERING INFORMATION

Item # / Article #	Price Book Description (EN)	UOM	Order Minimum	Order Multiple	Case Pack
N75001L	Organic Vapor Cartridge	PR	18	18	18
N75002L	Chlorine, Hydrogen Chloride, Sulfur Dioxide, Hydrogen Fluoride, Chlorine Dioxide, Formaldehyde Cartridge	PR	18	18	18
N75003L	Organic Vapor, Chlorine, Hydrogen Chloride, Sulfur Dioxide, Hydrogen Fluoride, Hydrogen Sulfide, Chlorine Dioxide Cartridge	PR	18	18	18
N75004L	Ammonia, Methylamine Cartridge	PR	18	18	18
N750052L	Mercury Vapor & Chlorine Cartridge with End of Service Life Indicator for Mercury Vapor	PR	18	18	18
75SCL	Defender: Organic Vapor, Chlorine, Hydrogen Chloride, Sulfur Dioxide, Hydrogen Sulfide, Hydrogen Fluoride, Chlorine Dioxide, Ammonia, Methylamine, Formaldehyde Cartridge	PR	18	18	18
7581P100L	Organic Vapor and P100 Cartridge/Filter Combination	PR	12	12	12
7582P100L	Chlorine, Hydrogen Chloride, Sulfur Dioxide, Hydrogen Fluoride, Chlorine Dioxide, Formaldehyde and P100 Cartridge/Filter Combination	PR	12	12	12
7583P100L	Organic Vapor, Chlorine, Hydrogen Chloride, Sulfur Dioxide, Hydrogen Fluoride, Hydrogen Sulfide, Chlorine Dioxide and P100 Cartridge/Filter Combination	PR	12	12	12
7584P100L	Ammonia, Methylamine and P100 Cartridge/Filter Combination	PR	12	12	12
75852P100L	Mercury Vapor, Chlorine and P100 Cartridge/Filter Combination, with End of Service Life Indicator for Mercury Vapor	PR	12	12	12
75SCP100L	Defender: Organic Vapor, Chlorine, Hydrogen Chloride, Sulfur Dioxide, Hydrogen Sulfide, Hydrogen Fluoride, Chlorine Dioxide, Ammonia, Methylamine, Formaldehyde and P100 Cartridge/Filter Combination	PR	12	12	12



by Honeywell

Honeywell Safety Products

900 Douglas Pike
Smithfield, RI 02917
Telephone: 800.430.4110 USA
www.honeywellsafety.com

CANADA
10550 Parkway Blvd
Anjou, Quebec H1J 2K4
Tel: 888.212.7233
Fax: 888.667.8477

LATIN AMERICA
tel: 514.905.3715
fax: 514.351.2645

MEXICO
tel: (01152) 55.9138.3491
fax: (01152) 55.9138.3492
Mexico Local Only:
01800.788.3074