



ITEM	PART #	DESCRIPTION	R/Q	QTY
1	30-3157	HEX NYLON LOCKNUT-ZINC M6-1.0		1
2	28-0002	WASHER-ZI SAE TYPE A 1/4"		1
3	14-0118	ISOLATOR - Ø 1 1/4" x 2" TALL		1
4	27-2931	PPHMS - M6-1.0 X 50MM		1
5	27-8501	HHCS-ZI GR 8.8 M12-1.25 X 35MM		2
6	28-0006	WASHER - ZI SAE TYPE A 1/2		6
7	14-0141	CASTORS 75mm x 25mm		2
8	30-3160	HEX NYLON LOCKNUT-ZINC M12-1.75		2
9	5-0340A77	FRAME - DPW4000		1
10	27-8060	HHCS-ZI GR 8.8 M10-1.5P X 16mm		4
11	29-0009	LOCKWASHER - MED 7/16		4
12	14-0140	VIB/ISO 30mm X 30mm HEIGHT		4
13	28-0003	WASHER-ZI SAE TYPE A 5/16"		8
14	30-3156	HEX NYLON LOCKNUT M8 X 1.25P X 6mm		4
15	20-1385A77	RIGHT AXLE BRACKET		1
16	28-0008	WASHER-ZI SAE TYPE A 5/8"		2
17	14-0139	WHEEL-10" RUBBR-SOLID GREY RIM		2
18	33-0351	COLLAR - 5/8" I.D. STEEL		2
19	27-8032	HHCS-ZI GR 8.8 M8-1.25P X 20MM		4
20	30-3158	HEX NYLON LOCKNUT-ZINC M4-0.7		2
21	18-0393	NOZZLE 15035 QC		1
-	18-0395	NOZZLE 25035 QC		1
-	18-0396	NOZZLE 40035 QC		1
22	33-0001	GROMMET 1/2 X 3/4 X 1/8		3
23	15-0342	HIGH PRESSURE HOSE - 1/4" X 27.5" 4000 PSI	X	1
24	22-0491	3 WAY BALL VALVE - 3/8" FNPT 7350PSI		1
25	20-1384A77	VALVE BRACKET		1
26	24-0105	ELBOW 90° - STEEL - 3/8M x 3/8F		2
27	15-0341	HOSE-3/8" x 33' 4000 PSI		1
28	17-0004	QC 3/8FX3/8 SOCKET BRASS		1
29	27-8001	BOLT - HHCS M6 - 1.00P x 15mm		4
30	29-0006	LOCK WASHER - 1/4"		4
31	15-0197	HOSE - 3/8 ID X 3/8 M SWIVEL X 3/8M X 28"		1
32	23-0096	SWIVEL - 3/8 M x 3/4 F GARDEN HOSE - BRASS		1
33	23-0047	COUPLING 1/4F X 3/8F HEX BRASS		1
34	42-0059	CLIP-SPRING WAND HOLDER		1
35	27-2770	PPHMS M4-0.7X16MM - SS		2
36	23-0120	HOSE BARB 1/4" M NPT x 1/2" - BRASS		1
37	42-0011	SS WORM CLAMP 3/8"-1"		1
38	15-0007	HOSE 1/2 250psi	2.583'	1
39	20-1386A77	LEFT AXLE BRACKET		1

M:\Drawings\PRIVATE LABEL\MAKINEX\DPW-4000\DPW-4000 FRAME ASSY.iam

Mi-T-M Corporation

SCALE: NTS	DATE: 6/26/20	DRAWING SIZE: B	APPD:	DRAWN BY: ATL
------------	---------------	-----------------	-------	---------------

DPW-4000 FRAME ASSY

DRAWING/PART NO: DPW-4000 FRAME ASSY