


REVISIONS

PRINT MAY BE REDUCED - DO NOT SCALE.

REV.	DESCRIPTION	DATE
------	-------------	------



ITEM NO.	PART NO.	PART NAME	QTY
1	TSHC-HS-US-V2	TILE SMASHER HEAD COMBO HILTI HEX SHANK V2	1
2	TSH-B	TSH BLADE	1
3	TSH-BS-V2	TSH SERRATED FLANGE BOLT	3



Sydney (Head Office) Ph: 1300 795 953
 15 Waltham St Fax: (02) 9439 9815
 Artarmon, 2064 www.makinex.com.au
 NSW, Australia sales@makinex.com.au

COPYRIGHT 2019 MAKINEX.
 WARNING: Copyright in this drawing remains the property of Kennards Innovation and Sustainability and copying in whole or part is not permitted without the written authority of the copyright owner.

GENERAL TOLERANCES
 (Unless otherwise noted)
 0-100mm: ± 0.25 mm
 100mm - 500mm: ± 0.5 mm
 500mm +: ± 1.0 mm
 Angular: ± 1 deg.

Third Angle Projection
 - AS 1100

DATE: 9/28/2020

SCALE: 1:5 A3

All Dimensions are in Millimetres
 Break All Sharp Corners and
 Remove Burrs & Swarf

25
 Denotes Critical Dimension

PROJECT:

DWG NO.

TSHC-HS-US-V2

NOTES:

TITLE

Tile Smasher Combo with HILTI HEX shank

MATERIAL

SEE PARTS

REV: 001

DRN:

FINISH

SEE PARTS

SHEET 1 OF 1