



PRODUCT DESCRIPTION

A refreshing take on reflector shades from the early days of Mid Century modern design, the Tahoe thoughtfully applies LED light to a classic concept. The LED housing that shines light against its metal shade painted white on its interior for better reflection is also punctured with a hole at its apex to cast light on the square-tubed yoke supporting it. Much more angular than the traditional reflecting up-light shaded pendant, this pendant brings more function to its fashion. A convenient LED lamp is also included facing down to illuminate the space below. Finished in a striking Black and Satin Brass combination, this pendant certainly calls attention while casually existing in its space.

MEASUREMENTS

DIMENSION : 18" W x 18.5" H
 MAX OAH : 60.5" OAH
 CANOPY : 5" W x 0.75" H
 HANGING WEIGHT : 4.96 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 900 Rated (500 Del.)
 BULB : 2 x 7W LED GU10 , 7W Total
 BULB INCLUDED : (Included)
 DIMMABLE : Yes
 CRI : 90 CRI
 COLOR_TEMP : 3000K
 LIGHTING_DIRECTION : Up/Down

FINISHES OPTION

 Black / Satin Brass

MATERIAL

Aluminum + Steel

RATINGS

cETLus
 Dry Location
 JA8 Bulb In



ADDITIONAL

SLOPE: 90
 RATED LIFE 25000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com