

**PRODUCT DESCRIPTION**

Drum shades in a variety of fabrics and materials are a core lighting offering. Flush mounts, pendants, and ADA sconces are available in options of linen, organza, grasscloth, and sound absorbing grey felt shades. An internal acrylic diffuser, illuminated by an evenly dispersed powerful LED light source, directs light downward and produces an ambient glow inside the outer shade. This lens features a crisp and tidy twist-lock mechanism that eliminates any visible hardware. whether it is put in a residential or commercial context, this collection meets the necessary application needs while adding style to the space.

MEASUREMENTS

DIMENSION : 13" W x 8.25" H x 3.75" Ext
MAX OAH : 13" W x 8.25" H
HANGING WEIGHT : 2.25 lb

LAMPING

INPUT VOLTAGE : 120-277V
LUMENS : 680 Rated (550 Del.)
BULB : 1 x 10W LED DC Integrated , 10W Total
BULB INCLUDED : (Integrated)
DIMMABLE : Triac & ELV dimmer
CRI : 90 CRI
COLOR_TEMP : 3000K
LIGHTING_DIRECTION : Omni

FINISHES OPTION

 Black Organza
 Grass Cloth
 Oatmeal
 White Linen

MATERIAL

Fabric, Polycarbonate, Steel

RATINGS

cETLus
Dry Location
Energy Star
ADA

**ADDITIONAL**

INSTALL UP/DOWN: Up
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com