



PRODUCT DESCRIPTION

A steel framed acrylic shade transitional flush mount available in a variety of finishes and sizes. Featuring easy accessibility to the shade after installation, the locking mechanism that shade's frame rests on top of making removal quick for keeping clean and replacing lamps over its lifetime. For those who prefer not to re-lamp, an LED option enhances the fixture by evenly dispersing the light across the shade, and it includes additional options made for light commercial applications. This includes an emergency backup battery and range voltage inputs. Available in your choice of Satin Nickel, Satin Brass, and Black and two shade sizes.

MEASUREMENTS

DIMENSION : 13" L x 13" W x 5" H
 HANGING WEIGHT : 4.63 lb

LAMPING

INPUT VOLTAGE : 120-277V
 LUMENS : 1,440 Rated (1,120 Del.)
 BULB : 1 x 16W LED PCB Integrated , 16W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : Triac
 CRI : 90 CRI
 COLOR_TEMP : 3000K
 LIGHTING_DIRECTION : Down

FINISHES OPTION

-  Black
-  Satin Brass
-  Satin Nickel

GLASS

White WT

MATERIAL

Steel

RATINGS

cETLus
 Dry Location
 Energy Star
 CA Title 24



ADDITIONAL

INSTALL UP/DOWN: UP
 RATED LIFE 50000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com