




PRODUCT DESCRIPTION

A glossy White glass shade, conical in form, is combined with sharp-lined bands of metal finished in your choice of Polished Nickel or Satin Brass to create a pyramid of softly diffused light. Squared off trapezoidal chain loops connect to squared chain links allowing for over ten feet of adjustment. Though modern with its angular form, this pendant applies traditional metalwork details to create a timeless piece perfect for over a kitchen island or bedside.



MEASUREMENTS

- DIMENSION : 5" L x 5" W x 8.5" H
- MAX OAH : 46.5" OAH
- CANOPY : 5" W x 0.86" H x 5" L
- HANGING WEIGHT : 3.04 lb

LAMPING

- INPUT VOLTAGE : 120V
- BULB : 1 x 60W Incandescent E26 , 40W Total
- BULB INCLUDED : (Not Included)
- DIMMABLE : Y

FINISHES OPTION

-  Polished Nickel
-  Satin Brass

GLASS

White WT

MATERIAL

Steel + Glass

RATINGS

cETLus
Dry Location



ADDITIONAL

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com