



PRODUCT DESCRIPTION

A glossy White glass shade, conical in form, is combined with sharp-lined bands of metal finished in your choice of Polished Nickel or Satin Brass to create a pyramid of softly diffused light. Squared off trapezoidal chain loops connect to squared chain links allowing for over ten feet of adjustment. Though modern with its angular form, this pendant applies traditional metalwork details to create a timeless piece perfect for over a kitchen island or bedside.

MEASUREMENTS

DIMENSION : 15.5" L x 15.5" W x 23" H
 MAX OAH : 63.75" OAH
 CANOPY : 5.5" W x 2.25" H x 5.5" L
 HANGING WEIGHT : 7.5 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y

FINISHES OPTION

 Polished Nickel
 Satin Brass

GLASS

White WT

MATERIAL

Steel, Glass

RATINGS

Dry Location



ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.